

Specifications



Eaton 1004771BCH

Eaton meter socket, 3 in bolt-on hub, 320A, Overhead/underground, #4-600 kcmil, Four-jaw, Single-phase, #4-600 kcmil, Lever bypass, Sockets:1, Three-wire, Ringless, 600V

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	1004771BCH
UPC	786685160184
PRODUCT LENGTH/DEPTH	5.68 in
PRODUCT HEIGHT	36.63 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	3 in bolt-on hub
AMPERAGE RATING	320A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TX : City Public Service of San Antonio (CPSB)
LINE	#4-600 kcmil
LOAD	#4-600 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3 in bolt-on hub
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1004771BCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



Specifications



Eaton 1004771BCH

Eaton meter socket, 3 in bolt-on hub, 320A, Overhead/underground, #4-600 kcmil, Four-jaw, Single-phase, #4-600 kcmil, Lever bypass, Sockets:1, Three-wire, Ringless, 600V

General specifications

PRODUCT NAME	Eaton meter socket
CATALOG NUMBER	1004771BCH
UPC	786685160184
PRODUCT LENGTH/DEPTH	5.68 in
PRODUCT HEIGHT	36.63 in
PRODUCT WIDTH	15 in
PRODUCT WEIGHT	5 lb
WARRANTY	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
CERTIFICATIONS	UL Listed

Product specifications

TYPE	3 in bolt-on hub
AMPERAGE RATING	320A
FEED TYPE	Top/bottom
NUMBER OF JAWS	Four-jaw
PHASE	Single-phase
UTILITY APPROVALS	TX : City Public Service of San Antonio (CPSB)
LINE	#4-600 kcmil
LOAD	#4-600 kcmil
NUMBER OF WIRES	Three-wire
HUB TYPE	3 in bolt-on hub
SECURITY	Ringless
VOLTAGE RATING	600 V
BYPASS	Lever
NUMBER OF SOCKETS	1

Resources

CATALOGS	Residential and Light Commercial, Metering Products, Volume 1 Tab 4
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - 1004771BCH
WARRANTY GUIDES	Selling Policy 25-000 - Distribution and Control Products and Services

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

