

**Open Switches**  
**T&B Catalog Number:**

OT100F3  
80432541587  
Active

**UPC Number:**  
**Status:**  
**Description:**

3 pole, 100 amps rated at 600 VAC, UL 98, open non-fusible disconnect switch

**Features**

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

**Application**

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.  
Motor feeder applications and motor feeder short circuit and ground fault protection

**General**

Number of Poles 3  
Series Non-fusible

**Approvals**

UL Class UL 98

**Dimension Information**

H x W x D (inches) 3.94 x 2.76 x 2.93

**Specifications**

Rated Current (Amps) 100  
Rated Voltage AC 600

**Packaging**

T&B Inner Pack 1  
Package in Units 10  
T&B Sold in UOM Each  
T&B Weight Per UOM 2.07 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com

**Open Switches**  
**T&B Catalog Number:**

OT100F3  
80432541587  
Active

**UPC Number:**  
**Status:**  
**Description:**

3 pole, 100 amps rated at 600 VAC, UL 98, open non-fusible disconnect switch

**Features**

Quick make, quick brake mechanism  
Extremely compact size  
Finger-proof construction with no hazardous exposed parts

**Application**

Suitable for use as motor disconnects or industrial control panel disconnects on service entrance equipment, panelboards, switchboards, industrial control equipment, motor control centers, etc.  
Motor feeder applications and motor feeder short circuit and ground fault protection

**General**

Number of Poles 3  
Series Non-fusible

**Approvals**

UL Class UL 98

**Dimension Information**

H x W x D (inches) 3.94 x 2.76 x 2.93

**Specifications**

Rated Current (Amps) 100  
Rated Voltage AC 600

**Packaging**

T&B Inner Pack 1  
Package in Units 10  
T&B Sold in UOM Each  
T&B Weight Per UOM 2.07 lbs. Each

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: techsupport@tnb.com