



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T101 Black Flush Operator

Eaton Corp

Catalog Number	10250T101
Manufacturer	Eaton Corp
Description	Black Flush Operator, 10250T Series, Momentary Switch Action, Non-Illuminated, Black, Plastic (Actuator) Material, 1.9 X 1.9 X 2.2 In Size, 0.22 LB
Weight per unit	0.2200 (lbs/each)
Product Category	Push Button Components

Features

bezel	Chrome
dimensions	48.2600millimetreX45.7200millimetreX55.8800millimetre
illumination	Non-illuminated
Operating Mode	Momentary
Rating	NEMA 3, 3R, 4, 4X, 12, 13

Material, Color, and Finish

actuator color	Black
----------------	-------

Descriptions

Description	BLACK FLUSH OPERATOR
-------------	----------------------

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113203270
UPC	782113203270

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
igcc	5210
Type	30.5 mm, Heavy-Duty
unspsc code	39122216

Packaging

Carton	1
Package	10
Weight Per each	0.22

Uses, Certifications, and Standards

Mounting	FLUSH
standard	UL Listed; CSA Certified; CE Marked



Powering Business Worldwide

pe.eaton.com

30.5 mm, Heavy-Duty Pushbutton Operator

10250T101

UPC:782113203270

Dimensions:

- **Height:** 2.2 IN
- **Length:** 1.9 IN
- **Width:** 1.8 IN

Weight: .22 LB

Warranties:

- 1 year

Specifications:

- **Type:** 30.5 mm, Heavy-Duty
- **Actuator Color:** Black
- **Actuator Material:** Plastic
- **Bezel:** Chrome
- **Illumination:** Non-illuminated
- **Mounting:** Flush
- **Operating Mode:** Momentary
- **Rating:** NEMA 3, 3R, 4, 4X, 12, 13
- **Series:** 10250T

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [Eaton Specification Sheet - 10250T101](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance:

- CE Marked

