



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



10250T11251 Extd PB R 1NC

Eaton Corp

Catalog Number	10250T11251
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton 30.5 MM Assembled Pushbutton, 10250T, Heavy-Duty, Nema 3, 3R, 4, 4X, 12, 13, Non-Illuminated, Momentary, Extended, Red Actuator, 1NC, Chrome Bezel, Plastic Actuator, Factory Assembled
Weight per unit	0.3500 (lbs/each)
Product Category	Push Button Complete Assemblie

Features

action	Red
actuator	Extended
Contact Configuration	1 NC
dimensions	2.5300 IN X 1.3800 IN X 1.3800 IN
media	Yes

Dimensions and Weight

Depth	2.53
Height	1.38
Width	1.38

Descriptions

Description	EXTD PB R 1NC
extra long description	ETN 10250T112-51 EXTD PB R 1NC
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton 30.5 mm Assembled pushbutton, 10250T, Heavy-Duty, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Momentary, Extended, Red actuator, 1NC, Chrome bezel, Plastic actuator, Factory assembled
Product Type	Extd PB R 1NC

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113259024
Manufacturers Part Number	10250T112-51
Model	Pushbutton
UPC	782113259024



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description OILTIGHT OPERATORS.30MM

Type PUSHBUTTON

Packaging

Carton 1

Weight Per each 0.35

Uses, Certifications, and Standards

Application Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels and OEMs

standard UL Listed, CSA Certified, CE Marked