



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 10250T197LRP2A Ind Light FV 120VAC Red Led - Plastic Lens

*Eaton Corp*

Catalog Number	10250T197LRP2A
Manufacturer	Eaton Corp
Description	Eaton Heavy-Duty Watertight and Oiltight Indicating Light, Heavy-Duty Watertight and Oiltight, Standard Actuator, Led, Full Voltage, Nema 3, 3R, 4, 4X, 12, 13, Red, Plastic, 120 V, 30.5 MM
Weight per unit	0.4000 (lbs/each)
Product Category	Pilot Light Complete Assemblie

### Features

dimensions	2.4000 IN X 2.1000 IN X 2.0000 IN
media	Yes

### Material, Color, and Finish

Style	30.5 mm
-------	---------

### Descriptions

Description	IND LIGHT FV 120VAC RED LED - PLASTIC LENS
extra long description	ETN 10250T197LRP2A IND LIGHT FV 120
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton Heavy-duty watertight and oiltight Indicating Light, Heavy-duty watertight and oiltight, Standard actuator, LED, Full voltage, NEMA 3, 3R, 4, 4X, 12, 13, Red, Plastic, 120 V, 30.5 mm
Product Type	Ind Light FV 120VAC RD Led-Plastic Lens

### Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782114711149
Manufacturers Part Number	10250T197LRP2A
UPC	782114711149

### Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON

### Packaging

Carton	1
Weight Per each	0.4



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

Application

Elec Assemblies, Panels & OEM - Electrical Assemblies, Panels  
and OEMs

standard

CSA Certified,UL Listed,CE Marked