ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

10250T173 JMB MSHD PB G

Eaton Corp

Catalog Number	10250T173
Manufacturer	Eaton Corp
Description	Eaton 10250T Pushbutton, 10250T, 30.5 MM, Heavy-Duty, 65 MM, Nema 3, 3R, 4, 4X, 12, 13, Non-Illuminated, Momentary, Jumbo Mushroom , Green Actuator, Chrome Bezel, Anodized Aluminum Actuator
Weight per unit	0.3000 (lbs/each)
Product Category	Push Button Components

Features

actuator	Jumbo mushroom
dimensions	2.4000 IN X 2.4000 IN X 2.1000 IN
media	Yes

Dimensions and Weight

Depth	2.4000
Height	2.1000
Size	65 mm
Width	2.4000

Descriptions

Description	JMB MSHD PB G
extra long description	ETN 10250T173 JMB MSHD PB G
Features	Eaton's 10250T line of 30.5 mm pushbuttons features a heavy-duty zinc die cast construction. Reliability nibs improve contact reliability even under dry circuit and fine dust conditions. In addition, drainage holes prevent the buildup of liquid inside the operator, which can prevent operation in freezing environments.
Long Description	Eaton 10250T pushbutton, 10250T, 30.5 mm, Heavy-Duty, 65 mm, NEMA 3, 3R, 4, 4X, 12, 13, Non-illuminated, Momentary, Jumbo mushroom , Green actuator, Chrome bezel, Anodized aluminum actuator
Product Type	JMB MSHD PB G

Manufacturer Information

Brand	Eaton
GTIN	00782113203409
Manufacturers Part Number	10250T173
Model	Pushbutton
UPC	782113203409

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	OILTIGHT OPERATORS.30MM
Type	PUSHBUTTON

Packaging

Carton	1
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Elec Assemblies, Panels & EOEM - Electrical Assemblies, Panels and EOEMsStationary Machinery and Equipment Outside Factory - Stationary Machinery and Equipment Outside Factory - Other
standard	UL Listed,CSA Certified,CE Marked