



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 107 2-1/2" Flex 90DEG Conn 5-PK

Topaz - Southwire LLC

Catalog Number	107
Manufacturer	Topaz - Southwire LLC
Description	Flexible Conduit Connector, 90 Degree Type; Zinc Die-Cast Material; 7.187 Inch; Squeeze Installation; UL (Canada and Us) Approval; 5 Standard Package; 2-1/2 Inch Trade Size; 2.45 to 2.98 Inch Cord Size; Non-Insulated Throat Type
Weight per unit	2.1 (lbs/each)
Product Category	Liquid Tight Fittings

### Features

Cable/Conduit Type	Steel and Aluminum Armored/Metal Clad Cable, Flexible Cord, Flexible Metal Conduit
Cord Size	2.45 TO 2.98 INCH
Material	Zinc Die-Cast
Throat Type	Non-Insulated

### Dimensions and Weight

Length	7.187 Inch
--------	------------

### Descriptions

Additional Information	Application Indoor, Dry Location; Strap Material Zinc Plated Steel; Number of Screws 4
Commodity Description	LIQUID TIGHT FLEX. CONDUIT FITTINGS
Description	2-1/2" FLEX 90DEG CONN 5-PK
extra long description	90 DEGREE TYPE; DIE-CAST ZINC MATERIAL; 7.187 INCH; (4) SCREW, SQUEEZE INSTALLATION; UL (CANADA AND US), UL 514B APPROVAL; 5 PER CASE STANDARD PACKAGE; 2-1/2 INCH TRADE SIZE; 2.45 TO 2.98 INCH CORD SIZE; NON-INSULATED THROAT TYPE; AC AND STEEL MC CABLE, FLEXIBLE METALLIC CONDUIT; SINGLE CABLE OPENING; STRAP MATERIAL ZINC PLATED STEEL; THREAD SIZE 0.875 INCH; APPLICATION INDOOR, DRY LOCATION; APPLICABLE STANDARD FEDERAL SPECIFICATION W-F-406E, W-F-406D
Long Description	FLEXIBLE CONDUIT CONNECTOR, 90 DEGREE TYPE; ZINC DIE-CAST MATERIAL; 7.187 INCH; SQUEEZE INSTALLATION; UL (CANADA AND US) APPROVAL; 5 STANDARD PACKAGE; 2-1/2 INCH TRADE SIZE; 2.45 TO 2.98 INCH CORD SIZE; NON-INSULATED THROAT TYPE
Product Type	Flexible Conduit Connector



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Southwire Rough Electrical Com
GTIN	00751338104105
UPC	751338104105

## Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	90 Degree

## Trade Size

Trade Size	2-1/2 INCH
------------	------------

## Packaging

Carton	1
Standard Package	5 in
Weight Per each	2.13

## Uses, Certifications, and Standards

Approval	UL (CANADA AND US)
Installation	SQUEEZE