



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1  
78626-0000, TX Georgetown  
Phone: 737-444-2615  
Fax: 737-444-2617



## 1226W Switch Maintd Control 20A 120/277V (DPDT) WH

*Pass & Seymour/Legrand*

Catalog Number	1226W
Manufacturer	Pass & Seymour/Legrand
Description	Double-Pole, Double-Throw Switch, 20A, 120/277V.
Weight per unit	0.3120 (lbs/each)
Product Category	Manual Motor Switches & Accy.

### Features

amperage rating	20
Contact Configuration	NO
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Xenon, LED, Fluorescent, Universal, Halogen, Incandescent, CFL
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	2
Switch Type	Toggle
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	2
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Color	White
Finish	Matte

### Dimensions and Weight

Size	3.3"
------	------

### Descriptions

Description	SWITCH MAINTD CONTROL 20A 120/277V (DPDT) WH
extra long description	P&S 1226W SW MAINTD CNTRL 20A 120/
Features	Durable
Long Description	Double-Pole, Double-Throw Switch, 20A, 120/277V.
Product Type	SW Maintd CNTRL 20A 120/277V (DPDT) W
Special Features	Oversized silver alloy contacts, side wired, can be mounted in standard device box\



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2450 NE Inner Loop Building 1  
78626-0000, TX Georgetown  
Phone: 737-444-2615  
Fax: 737-444-2617

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007122640
Manufacturers Part Number	1226-W
UPC	785007122640

## Taxonomies, Classifications, and Categories

Category Description	REVERSING
Type	Manual Controller

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.312

## Uses, Certifications, and Standards

Application	Industrial
Enclosure	Box or NEMA 1 sheet steel
Mounting standard	WALL CULUS, UL, CSA, UL listed