



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **12124SCG Encl 12X12X4 N3 N12 Galv SC Gasketed** *Cooper B-Line/Cable Tray*

Catalog Number	12124SCG
Manufacturer	Cooper B-Line/Cable Tray
Description	Eaton B-Line Series Type 3/3R Junction Boxes, 12" Height, 4" Length, 12" Width, Nema 3 and 12, Screw Cover, SCG Enclosure, Surface Mounted, Small Single Door, No Mounting Provisions, Galvanized Steel, Oil-Resistant Gasket, Gasketed Screws
Weight per unit	12.2 (lbs/each)
Product Category	Nema Types 3 & 3R Metallic Enc

### **Features**

dimensions	4.0000 IN X 12.0000 IN X 12.0000 IN
Material	Galvanized Steel
Mounting Type	Surface

### **Material, Color, and Finish**

Color	Gray
-------	------

### **Dimensions and Weight**

Size	12.00 In Width X 4.00 In Depth X 12.00 In Height
------	--

### **Descriptions**

Description	ENCL 12X12X4 N3 N12 GALV SC GASKETED
extra long description	B-LINE 12124 SCG TYPE 3 GLV GASKETE
Features	Eaton's B-Line series junction boxes provide reliable environmental protection and are used as commercial wiring, junction, pull, and termination boxes.
Long Description	Eaton B-Line series Type 3/3R junction boxes, 12" height, 4" length, 12" width, NEMA 3 and 12, Screw cover, SCG enclosure, Surface mounted, Small single door, No mounting provisions, Galvanized steel, Oil-resistant gasket, gasketed screws
Product Type	Type 3 GLV Gasketed SC 12X12X4

### **Manufacturer Information**

Brand	Eaton
GTIN	00782051108637
Manufacturers Part Number	12124 SCG
UPC	782051108637

### **Taxonomies, Classifications, and Categories**

Category Description	STEEL JUNCTION BOXES
Type	Type 3/3R junction boxes



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	12.2

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Safety and Security SystemsCommercial / Institutional Buildings / Structures - Lighting and Lighting ControlsCommercial / Institutional Buildings / Structures - Critical PowerCommercial / Institutional Buildings / Structures - Commercial/Inst Bldg Structures - AftermarketAviationCommercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - OtherCommercial / Institutional Buildings / Structures - Power Distribution
nema rating	312
standard	CSA C22.2, NEMA, UL 50