



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636



124TZ 1/2 Beam Clamps Zinc

Topaz - Southwire LLC

Catalog Number	124TZ
Manufacturer	Topaz - Southwire LLC
Description	Beam Clamp, Single U Type; Malleable Iron Material; 1-1/8 Inch Max. Jaw Capacity; 600 LB Load Capacity; 1/2 Inch-13 Tpi Screw Size; Square Head Screw Type; Yes Supplied With Screw; Size 2.5 Inch L X 2.53 Inch W X 2.14 Inch H
Weight per unit	N/A
Product Category	Anchors & Fasteners

Features

Load Capacity	600 LB
Material	Malleable Iron
Maximum Jaw Capacity	1-1/8 INCH
Screw Size	1/2 Inch-13 TPI
Screw Type	Square Head
Supplied with Screw	YES

Descriptions

Additional Information	Size 2.5 Inch L x 2.53 Inch W x 2.14 Inch H
Commodity Description	ANCHORS & FASTENERS
Description	1/2 BEAM CLAMPS ZINC
extra long description	1-SCREW, 2-HOLE TYPE; MALLEABLE IRON MATERIAL; ZINC PLATED FINISH; 1-1/8 INCH MAX. JAW CAPACITY; SUPPORTS THREADED ROD, THREADED BRINDLE RINGS AND ELECTRICAL BOXES APPLICATION; 600 POUND LOAD CAPACITY; 1/2 INCH-13 TPI SCREW SIZE; SQUARE HEAD SCREW TYPE; YES SUPPLIED WITH SCREW; ROHS COMPLIANT; OVERALL DIMENSION 2.53 INCH LENGTH X 2.14 INCH WIDTH X 2.5 INCH HEIGHT; TIGHTEN TORQUE 250 INCH
Long Description	BEAM CLAMP, SINGLE U TYPE; MALLEABLE IRON MATERIAL; 1-1/8 INCH MAX. JAW CAPACITY; 600 LB LOAD CAPACITY; 1/2 INCH-13 TPI SCREW SIZE; SQUARE HEAD SCREW TYPE; YES SUPPLIED WITH SCREW; SIZE 2.5 INCH L X 2.53 INCH W X 2.14 INCH H
Product Type	Beam Clamp

Manufacturer Information

Brand	TOPAZ ELECTRIC CORP
Manufacturers Part Number	124TZ



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

520 Equity Ave
72032-0000, AR Conway
Phone: 501-336-8444
Fax: 501-329-5636

Taxonomies, Classifications, and Categories

Category Description Fuses & Fuse Accessories

Type SINGLE U

Packaging

Carton 1

Package 25

Weight Per each 0