



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106



121272GRTNK 12X12X72 RT Wireway *Unity Manufacturing*

Catalog Number	121272GRTNK
Manufacturer	Unity Manufacturing
Description	Unity 121272GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 12 In, 12 In Depth, Length: 72 In, 14 Ga Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, Nema 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UI 50 and UI 870 - Type 3R: Intended For Outdoor Use Primarily to Provide A Degree Of Protection Against Rain, Sleet and Damage From External Ice Formation, Csa C22.2 No. 26 Certified, Type 3R, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and T
Weight per unit	70.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

Features

Knockouts	NO
Material	Low-Carbon Steel

Material, Color, and Finish

Color	Gray
Finish	POLYESTER POWDER

Dimensions and Weight

Depth	12
Length	72
Width	12



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1570 Lionel Drive
79936-0000, TX El Paso
Phone: 915-995-8443
Fax: 915-245-2106

Descriptions

Description	12X12X72 RT WIREWAY
extra long description	UNT 121272GRTNK N3R SCREW COVER GUT
Long Description	Unity 121272GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 12 IN, 12 IN Depth, Length: 72 IN, 14 GA Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, NEMA 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And T
Product Type	N3R Screw Cover Gutter No K.O. Powder Coated
Special Features	For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket

Manufacturer Information

Brand	Unity
GTIN	00761515144961
Manufacturers Part Number	121272GRTNK
UPC	761515144961

Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	GRT Gutter Slip-On Cover Wiring Trough

Packaging

Carton	1
Weight Per each	70

Uses, Certifications, and Standards

Application	For Cable And Wire Junction, Distribution And Termination, Houses Runs Of Control And Power Cable
Enclosure standard	NEMA 3R, IP32 UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant