



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln  
79109-3210, TX Amarillo  
Phone: 806-220-0404  
Fax: 806-220-0811



## 121272GRTNK 12X12X72 RT Wireway *Unity Manufacturing*

Catalog Number	121272GRTNK
Manufacturer	Unity Manufacturing
Description	Unity 121272GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 12 In, 12 In Depth, Length: 72 In, 14 Ga Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, Nema 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UI 50 and UI 870 - Type 3R: Intended For Outdoor Use Primarily to Provide A Degree Of Protection Against Rain, Sleet and Damage From External Ice Formation, Csa C22.2 No. 26 Certified, Type 3R, IEC 60529, Rohs Compliant, For Cable and Wire Junction, Distribution and T
Weight per unit	70.0 (lbs/each)
Product Category	Nema Type 3R Trough & Gutter

### Features

Knockouts	NO
Material	Low-Carbon Steel

### Material, Color, and Finish

Color	Gray
Finish	POLYESTER POWDER

### Dimensions and Weight

Depth	12
Length	72
Width	12



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4000 Mockingbird Ln  
79109-3210, TX Amarillo  
Phone: 806-220-0404  
Fax: 806-220-0811

## Descriptions

Description	12X12X72 RT WIREWAY
extra long description	UNT 121272GRTNK N3R SCREW COVER GUT
Long Description	Unity 121272GRTNK GRT Gutter Slip-On Cover Wiring Trough, Width: 12 IN, 12 IN Depth, Length: 72 IN, 14 GA Low Carbon Steel, Gray Polyester Powder Thermoset Over Phosphatized Surface, NEMA 3R, IP32 Enclosure, Gunsmoke Gray Color, No Knockouts, UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant, For Cable And Wire Junction, Distribution And T
Product Type	N3R Screw Cover Gutter No K.O. Powder Coated
Special Features	For protecting wiring indoors from dripping water, or outdoors from rain, sleet and snow; Formed from code gauge, low carbon steel; Drip shield top, seam-free sides; Accumulation-free bottom; Embossed mounting holes provided; Slip-on cover without gasket

## Manufacturer Information

Brand	Unity
GTIN	00761515144961
Manufacturers Part Number	121272GRTNK
UPC	761515144961

## Taxonomies, Classifications, and Categories

Category Description	STEEL WIRE WAY JUNCTION BOXES
Type	GRT Gutter Slip-On Cover Wiring Trough

## Packaging

Carton	1
Weight Per each	70

## Uses, Certifications, and Standards

Application	For Cable And Wire Junction, Distribution And Termination, Houses Runs Of Control And Power Cable
Enclosure standard	NEMA 3R, IP32 UL 50 And UL 870 - Type 3R: Intended For Outdoor Use Primarily To Provide A Degree Of Protection Against Rain, Sleet And Damage From External Ice Formation, CSA C22.2 No. 26 Certified, Type 3R, IEC 60529, RoHS Compliant