



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 123100Y1 Stringlight, Navy HD W/ 100FT 12/3 Yel Seow Cable

*Ericson MFG*

Catalog Number	123100Y1
Manufacturer	Ericson MFG
Description	Stringlight, Navy HD W/ 100FT 12/3 Yel Seow Cable W/ 10 Lights Total. 1 Light Spaced Every 10FT. Pri = Nema 5-15P & Sec = Nema 5-15C. Led Bulbs & Guards Not Included
Weight per unit	21.7 (lbs/each)
Product Category	Lighting

### Features

bulb type	LED (Customer Supplied)
Cable Length	100
Cable Type	SEOW
lumens	Customer Supplied
max amps	15
Voltage Rating	12 to 240
Wattage	150

### Material, Color, and Finish

Color	Yellow
-------	--------

### Dimensions and Weight

Size	3.605 X 3.785
------	---------------

### Descriptions

Construction	Overall Length (FT) = 100, # of Sockets/Lights = 10, Length/Spacing between Sockets/Lights (FT) = 10
Description	STRINGLIGHT, NAVY HD W/ 100FT 12/3 YEL SEOW CABLE
extra long description	ERIC 123100Y-1 STNGLITE 12/3 SEOW 1
Long Description	STRINGLIGHT, NAVY HD W/ 100FT 12/3 YEL SEOW CABLE W/ 10 LIGHTS TOTAL. 1 LIGHT SPACED EVERY 10FT. PRI = NEMA 5-15P & SEC = NEMA 5-15C. LED BULBS & GUARDS NOT INCLUDED
Product Type	Stnglite 12/3 Seow 15A/120V 100' Navy
Special Features	12/3 AWG SEOW Cable, Nema 5-15 Plug/Heavy Duty Rubberized Connector, Weatherproof

### Manufacturer Information

Brand	ERICSON
GTIN	00782862562093
Manufacturers Part Number	123100Y-1
UPC	782862562093

### Taxonomies, Classifications, and Categories

Type	LIGHTING
------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Weight Per each	21.65

## Uses, Certifications, and Standards

standard	UL, CSA, CUL, OSHA
----------	--------------------