



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1251I Switch CTR Off Control 20A 120/277V (SPDT) Iv

Pass & Seymour/Legrand

Catalog Number	1251I
Manufacturer	Pass & Seymour/Legrand
Description	Manual Controller, 1 Pole, 20 A, 120/277 V Ac, Wall Mount, Steel Enclosure Material, Ivory, Toggle Actuator, 1.469 In Overall Length, 1.5 In Overall Width, 3.281 In Overall Height, Toggle Switch, Insulated, 0.26504 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

action	Single pole
actuator	Toggle Switch
amperage rating	20
connection	Side wire
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Xenon, Halogen, CFL, Fluorescent, Incandescent, Universal, LED
Material	Thermoplastic
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Toggle
throw type	Double Throw
Voltage	120/277 V
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	SWITCH CTR OFF CONTROL 20A 120/277V (SPDT) IV
extra long description	P&S 1251I SW CTR OFF CONTRL 20A 120



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007125115
Manufacturers Part Number	12511
UPC	785007125115

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Commercial
Enclosure	STEEL
Mounting	WALL
standard	CSA, UL, CULUS, UL 498