



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1251L Switch CTR Off Control 20A 120/277V (SPDT)

Pass & Seymour/Legrand

Catalog Number	1251L
Manufacturer	Pass & Seymour/Legrand
Description	Manual Controller, Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V, Locking.
Weight per unit	0.2750 (lbs/each)
Product Category	Manual Motor Switches & Accy.

Features

action	SP, DT
actuator	Toggle
amperage rating	20
Contact Rating	15Amp, 120/277V
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Universal, CFL, Halogen, LED, Fluorescent, Xenon, Incandescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Locking
throw type	Double Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Brown
Finish	Matte

Dimensions and Weight

Size	3.3"
------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	SWITCH CTR OFF CONTROL 20A 120/277V (SPDT)
extra long description	P&S 1251L SW CTR OFF CNTRL 20A 120/
Features	Durable
Long Description	Manual Controller, Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V, Locking.
Product Type	SW CTR Off CNTRL 20A 120/277V (SPDT)
Special Features	Side wire terminals, Fiber Terminal insulation barrier\

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007125122
Manufacturers Part Number	1251-L
UPC	785007125122

Taxonomies, Classifications, and Categories

Category Description	Industrial switches
Type	Manual Controller

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.275

Uses, Certifications, and Standards

Application	Industrial
Mounting	WALL
standard	CULUS, UL, CSA, UL listed