



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



1256 2" Weatherhead *Bridgeport Fittings*

Catalog Number	1256
Manufacturer	Bridgeport Fittings
Description	Clamp-On Entrance Cap, 2 In Trade Size, Aluminum, Plain, 4-7/16 In Length, 5-3/4 In Width, 1.6 LB/Ea
Weight per unit	1.6 (lbs/each)
Product Category	Service Entrance CBL Fittings

Features

Cable Entry fitting type	Phenolic entrance to Aluminum clamp type for Rigid/IMC
media	Clamp-On
	Yes

Dimensions and Weight

Size	2 In
------	------

Descriptions

Description	2" WEATHERHEAD
Special Features	1 hole 9/16" dia., 2 holes 3/4" dia., 3 holes 1" dia.

Manufacturer Information

Brand	Bridgeport
GTIN	00781747012562
UPC	781747012562

Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	Entrance Caps

Packaging


Carton	1
Package	5
Weight Per each	1.6

Uses, Certifications, and Standards

Application	Clamp type entrance cap for rigid conduit and IMC. 2 hole 9/16" dia.; 2 holes 3/4" dia.; 3 holes 1" dia.
standard	UL mA

Clamp-On Type

Images



Application

Clamp type entrance cap for rigid conduit and IMC. 2 hole 9/16" dia.; 2 holes 3/4" dia.; 3 holes 1" dia.

Product Information

Material: Aluminum
 Finish: Plain

Certifications & Codes:

NEMA Standard: FB-1
 UL File Number: E11259
 UL Standard: UL-514B
 UNSPSC: 39121311

[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 7

Dimension B in Inches: 5-3/4

Dimension C in Inches: 4-7/16

Catalog ID: 1256

UPC Number: 781747012562

Description: Entrance Cap, Clamp-On, Aluminum, Size 2 Inch

Application: Clamp type entrance cap for rigid conduit and IMC. 2 hole 9/16" dia.; 2 holes 3/4" dia.; 3 holes 1" dia.

Trade Size: 2"

Std Pkg Qty: 5

Unit Qty: Bulk