



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120  
75041-0000, TX Garland  
Phone: 214-503-7227  
Fax: 214-503-9766



## 13037LTWBOX Switch Toggle 3-Way LT 15A 120V GRD WH

*Eaton Wiring Devices*

Catalog Number	13037LTWBOX
Manufacturer	Eaton Wiring Devices
Description	Eaton Toggle Switch, #14-10 Awg, 15A, Flush, 120V, Back and Side, Push Wire, Screw, White, Load Type: Motor Control, Fan, Led, Incandescent, Elv, MLV, CFL, Flourescent, Halogen, Single-Pole, Three-Way, Three-Way
Weight per unit	0.1250 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	15
dimensions	1.3100 IN X 0.8800 IN X 3.2800 IN
Material	Polycarbonate
Poles	1
Voltage Rating	120 V

### Descriptions

Description	SWITCH TOGGLE 3-WAY LT 15A 120V GRD WH
extra long description	EWD 1303-7LTWBOX Switch Toggle 3-Wa
Features	Eaton's Arrow Hart residential grade switches are engineered for smooth action and years of safe, dependable service - no matter what the application, type of load or use.
Long Description	Eaton toggle switch, #14-10 AWG, 15A, Flush, 120V, Back and side, push wire, Screw, White, Load type: Motor Control, Fan, LED, Incandescent, ELV, MLV, CFL, Flourescent, Halogen, Single-Pole, Three-Way, Three-Way
Product Type	Switch Toggle 3-Way LT 15A 120V GRD WH
Special Features	Box

### Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664519482
Manufacturers Part Number	1303-7LTWBOX
UPC	032664519482

### Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	TOGGLE SWITCH

### Packaging

Carton	1
Package	100
Weight Per each	0.125



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3737 Grader Street Suite 120  
75041-0000, TX Garland  
Phone: 214-503-7227  
Fax: 214-503-9766

## Uses, Certifications, and Standards

Application

Residential Bldgs & Facilities - Residential Bldgs & Facilities -

Other

standard

cULus Listed,NOM,RoHS Compliant