



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street  
75964-7263, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 13053UN Fluor LH Med Bi-Pin Short Slide On

*Pass & Seymour/Legrand*

Catalog Number	13053UN
Manufacturer	Pass & Seymour/Legrand
Description	Fluorescent Lampholder, Slide-On Medium Bi-Pin Base, Fluorescent Lamp, Medium Lamp Size, 600 V Ac, 660 W, Plastic, White, Wire Terminal, Slide-On, 1.6875 In Height, 1.25 In Length, 1.375 In (Dia.) Width, 0.75 In Depth, 0.04 LB
Weight per unit	0.0360 (lbs/each)
Product Category	Linear Fluorescent Lampholders

### Features

Ballast Type	Fluorescent Ballast
Base	Slide -On

### Descriptions

Description	FLUOR LH MED BI-PIN SHORT SLIDE ON
-------------	------------------------------------

### Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007030532
UPC	785007030532

### Taxonomies, Classifications, and Categories

Category Description	Miscellaneous residential devices
Type	Bi-Pin Lampholder

### Packaging

Carton	10
Package	100
Weight Per each	0.036

### Uses, Certifications, and Standards

Frequency Rating	60 HZ
Mounting standard	Slide-On UL, CSA

---

## FLUORESCENT LAMPHOLDER

13053UN | [Pass & Seymour](#)



---

### FEATURES & BENEFITS

Slide-on, short, for medium bi-pin lamps with captive nut, 4 quick wire terminals. White.



- Quality Materials.
- Durability.
- Time-tested design.

---

### SPECIFICATIONS

#### GENERAL INFO

Type: Fluorescent Lampholders

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: Yes  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes  
UN SPSC: 39111803  
UR: No

#### DIMENSIONS

Depth (US): .75"  
Diameter (US): 1.375"  
Height (US): 1.6875"  
Width (US): 1.25"

## TECHNICAL INFORMATION

Volts: 600V

Watts: 660

## BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

