



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050



13150AL04 8" Diffuse Ac/DC Conn LT *Eaton Corp*

Catalog Number	13150AL04
Manufacturer	Eaton Corp
Description	Eaton Oem Prism 18MM Tubular Photoelectric Sensor, Diffuse Reflective, Forward Viewing, Output On, Dual Key Micro, 80 Ma Ac/100 Ma DC At 20-132V, 4 Pin, Isolated SSR, 20-132 Vac 50/60 HZ, 15-30 VDC
Weight per unit	0.6700 (lbs/each)
Product Category	Photoelectric Sensors

Features

connection	Dual key micro
------------	----------------

Dimensions and Weight

Height	0.71
Length	2.35
Width	0.47

Descriptions

Description	8" DIFFUSE AC/DC CONN LT
extra long description	ETN 13150AL04 8" DIFFUSE AC/DC CONN
Features	Prism series 18 mm tubular sensors provide a flexible isolated output and twice the optical gain of other sensors in this product class. These cost-effective sensors offer forward- and right-angle viewing models that feature identical gain and optical characteristics for the best fit.
Long Description	Eaton OEM Prism 18mm tubular photoelectric sensor, Diffuse Reflective, Forward Viewing, Output ON, Dual key micro, 80 mA AC/100 mA DC at 20-132V, 4 pin, Isolated SSR, 20-132 Vac 50/60 Hz, 15-30 Vdc
Product Type	8" Diffuse Ac/DC Conn LT

Manufacturer Information

Brand	EATON CUTLER-HAMMER
GTIN	00782113011325
Manufacturers Part Number	13150AL04
UPC	782113011325

Taxonomies, Classifications, and Categories

Category Description	PROXIMITY SWITCHES AND CORDSETS
Type	Tubular photoelectric sensor

Packaging

Carton	1
Weight Per each	0.67



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

10917 Mill Creek Rd
66219-0000, KS Lenexa
Phone: 913-563-7000
Fax: 913-563-7050

Uses, Certifications, and Standards

Application	Vehicles: On-Road - PickUp & Delivery: Food
Operating Temperature	-13° to 131°F (-25° to 55°C)
standard	UL Recognized,cUL Recognized