



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700



130C112X30FT Linerless Rubber Splicing Tape, 1-1/2" X 30', BK *Minnesota Mining (3M)*

Catalog Number	130C112X30FT
Manufacturer	Minnesota Mining (3M)
Description	Scotch® Tape 130C Is A Linerless 30 Mil Thick, Premium Grade, Rubber Splicing Tape Used For Splicing and Terminating Cables and Wires. It Withstands Temperatures Up to 194 °F (90 °C) With Emergency Overload Up to 266 °F (130 °C). The Tape Has Excellent Electrical and Mechanical Properties to Provide Moisture Seal Protection.
Weight per unit	0.9000 (lbs/each)
Product Category	Markers & Marking Tapes - Tape

Descriptions

Description	LINERLESS RUBBER SPLICING TAPE,1-1/2" X 30',BLACK
extra long description	3M 7000006086 Scotch® Linerless Rub
Features	Scotch® Tape 130C is a highly conformable tape that provides electrical and mechanical protection with the combination of an aggressive rubber resin adhesive and a self fusing, ethylene propylene backing. The tape provides primary insulation for solid, dielectric insulated cables rated through 69 kV. This tape is designed for low and high voltage, bus bar insulation, end sealing of cables and jacket repair applications. It has outstanding mechanical and electrical properties that offer moisture seal and v
Long Description	Scotch® Tape 130C is a linerless 30 mil thick, premium grade, rubber splicing tape used for splicing and terminating cables and wires. It withstands temperatures up to 194 °F (90 °C) with emergency overload up to 266 °F (130 °C). The tape has excellent electrical and mechanical properties to provide moisture seal protection.
Product Type	Scotch® Linerless Rubber Splicing Tape 130C
Special Features	provides excellent thermal dissipation of splice heat

Manufacturer Information

Brand	Scotch
GTIN	00054007417187
Manufacturers Part Number	7000006086
UPC	054007417187

Taxonomies, Classifications, and Categories

Category Description	TAPE
Type	linerless Ethylene Propylene Rubber



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

800 Old Boston Road
75501-0000, TX Texarkana
Phone: 903-223-6400
Fax: 903-223-6700

Availability

Status Inactive

Packaging

Carton 12

Weight Per each 0.9

Uses, Certifications, and Standards

Application High Voltage

standard ASTM D-4388 type 1, 2 & 3 HH-I-3825B