

LIGHTING HARDWARE

bulk & packaged

For every repair need, Westinghouse has you covered. From sockets to switches, canopies to crossbars, we have those hard to find parts to make your life easier.



Hardware comes either in retail package or bulk pack. Bulk pack has been indicated throughout the section.

Nipples & All Thread

THREAD SIZES

Thread sizes come in several different types:

- 1/4-27 is 1/4" in diameter and fits harps and most finials
- 1/8-IP is 3/8" in diameter and fits ordinary lamp sockets
- 1/4-IP is 1/2" in diameter and is used in floor lamps



70151
Six Assorted Nipples

Zinc-Plated

- Includes:
- 2 1/4-IP x 3/4"
 - 2 1/4-IP x 1 1/2"
 - 2 1/4-IP x 2"



70150
Eight Assorted Nipples

Zinc-Plated

- Includes:
- 2 1/8-IP x 1/2"
 - 2 1/8-IP x 1"
 - 2 1/8-IP x 1 1/2"
 - 2 1/8-IP x 2"


1/4-27



1/8-IP



1/4-IP



3/8-IP



* **13352**
Brass Hex Head Nipple
Threaded 1/8-IP
Thread 3/16" Long

Steel Nipples Zinc-Plated

- * **13416** - 2" Long
- * **13418** - 3" Long
- * **13420** - 4" Long
- * **13424** - 6" Long
- 70613** - 6" Long (*Carded 2-Pack*)
Threaded 1/4-IP



* **13650**
70270
30" Steel Brass-Plated All-Thread Pipe
Threaded 1/8-IP

* **13648**
Steel All-Thread Pipe
1/8-IP x 36"

Steel Nipples Zinc-Plated


- * **13204** - 1/2" Long
- * **13206** - 3/4" Long
- 70176** - 1" Long (*Carded 4-Pack*)
- * **13212** - 1 1/2" Long
- 70601** - 1 1/2" Long (*Carded 4-Pack*)
- * **13216** - 2" Long
- 70602** - 2" Long (*Carded 2-Pack*)
- * **13224** - 3" Long
- 70603** - 3" Long (*Carded 2-Pack*)
- * **13228** - 3 1/2" Long
- * **13232** - 4" Long
- 70604** - 4" Long (*Carded 2-Pack*)
- * **13248** - 6" Long
- 70606** - 6" Long (*Carded 2-Pack*)
Threaded 1/8-IP

* **13312** - 1 1/2" Long
Brass Running Thread Nipples
Threaded 1/8-IP

70272 12" All-Thread Lamp Pipe Kit

Zinc-Plated Steel

- Includes:
- 2 1/8-IP x 12" Threaded Pipe
 - 2 1/8-IP Couplings
 - 2 1/8-IP Locknuts
 - 2 1/8-IP Knurled Locknuts
 - 2 Washers



*Bulk Pack

CARDER PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com