

# Specifications

## Eaton 14002-2

Eaton Bussmann series power terminal block, 600 Vac, 600 Vdc, 115 A, Two-pole, SCCR: 10 kA

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series power terminal block
<b>CATALOG NUMBER</b>	14002-2
<b>UPC</b>	051712206990
<b>EAN</b>	5027590508063
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	0.5 in
<b>PRODUCT WEIGHT</b>	0.034 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Contact factory RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer
<b>PRODUCT TYPE</b>	Power terminal block



Powering Business Worldwide

## Electrical rating

AMPERAGE RATING	115A
SHORT-CIRCUIT RATING	SCCR: 10 kAIC
VOLTAGE RATING	600 Vac, 600 Vdc

## Physical details

NUMBER OF POLES	Two-pole
TYPE	Power terminal block

## Resources

	<a href="#">Bussmann series complete full line catalog no. 1007</a>
CATALOGS	<a href="#">14002-2~#80K (3 WKS)</a> <a href="#">Bussmann series full line catalog 1007, section 09 - power distribution blocks</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 14002-2</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton 14002-2

Eaton Bussmann series power terminal block, 600 Vac, 600 Vdc, 115 A, Two-pole, SCCR: 10 kA

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series power terminal block
<b>CATALOG NUMBER</b>	14002-2
<b>UPC</b>	051712206990
<b>EAN</b>	5027590508063
<b>PRODUCT LENGTH/DEPTH</b>	0.5 in
<b>PRODUCT HEIGHT</b>	0.5 in
<b>PRODUCT WIDTH</b>	0.5 in
<b>PRODUCT WEIGHT</b>	0.034 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Contact factory RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer
<b>PRODUCT TYPE</b>	Power terminal block



Powering Business Worldwide

## Electrical rating

AMPERAGE RATING	115A
SHORT-CIRCUIT RATING	SCCR: 10 kAIC
VOLTAGE RATING	600 Vac, 600 Vdc

## Physical details

NUMBER OF POLES	Two-pole
TYPE	Power terminal block

## Resources

	<a href="#">Bussmann series complete full line catalog no. 1007</a>
CATALOGS	<a href="#">14002-2~#80K (3 WKS)</a> <a href="#">Bussmann series full line catalog 1007, section 09 - power distribution blocks</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 14002-2</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc** Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2026 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

