



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3325 Clay Avenue  
76711-0000, TX Waco  
Phone: 254-752-3331  
Fax: 254-752-3460



## 1597TRWRLA Radiant Self Test TR WR GfcI 15A 125V La

*Pass & Seymour/Legrand*

Catalog Number	1597TRWRLA
Manufacturer	Pass & Seymour/Legrand
Description	Self-Test Duplex Receptacle, 15 A, 125 V, 2 Poles, #14 to #10 Awg Compatible Wire Size, Control Circuit Actuator, Back and Side Wired Connection, 60 HZ, 1.73 In Width, 4.20 In Height, Thermoplastic Material, Light Almond, 0.025 Sec Trip Time, Weather Resistant, 0.2800 LB
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### Features

actuator	Control Circuit
amperage rating	15
connection	Back and side wire
indoor/outdoor	Both
interrupt rating	4 to 6 mA
Mounting Type	Box
Number of Gangs	1.0
Number of Wires	3
Outlet Type	GFCI, Tamper-Resistant, Weather-Resistant
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage	125.0 V
Voltage Rating	125
Wall Plate Included	YES

### Material, Color, and Finish

Finish	SATIN
--------	-------

### Dimensions and Weight

Length	1.03
Width	1.73

### Descriptions

Description	RADIANT SELF TEST TR WR GFCI 15A 125V LA
extra long description	P&S 1597TRWRLA RADIANT SELF TEST TR

### Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007036497
UPC	785007036497



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3325 Clay Avenue  
76711-0000, TX Waco  
Phone: 254-752-3331  
Fax: 254-752-3460

## Taxonomies, Classifications, and Categories

Category Description	Residential GFCI devices
Type	Outlet

## Trade Size

Amperage	15.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.275

## Uses, Certifications, and Standards

environmental conditions	95% Humidity, UL 94 V2
Operating Temperature	-35°C to +66°C
standard	CULUS, UL, cULus, UL Listed, FSUL