



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6112 42nd Street
79407-0000, TX Lubbock
Phone: 806-698-6329
Fax: 806-698-6805



15W47 Straight Blade IP67 Conn 15A 125V 5-15R

Pass & Seymour/LeGrand

Catalog Number	15W47
Manufacturer	Pass & Seymour/LeGrand
Description	Rated Watertight For 1, 500 Psi High-Pressure Hosedown, Pass and Seymour Plugs and Connectors Feature Multiple Seals to Ensure Protection Against The Environment. Constructed Of A Sturdy Rubber Body, Which Makes Them Impact- and Chemical-Resistant, They Have Nickel-Plated Blades and Contacts For Superior Corrosion Resistance.
Weight per unit	0.4400 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	15
indoor/outdoor	Both
Material	Rubber
Number of Wires	3.0
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	14 - 12 AWG

Material, Color, and Finish

Color	Yellow
-------	--------

Dimensions and Weight

Size	4.75"
------	-------

Descriptions

Description	STRAIGHT BLADE IP67 CONN 15A 125V 5-15R
extra long description	P&S 15W47 STR BLADE IP67 CONN 15A 1
Features	Watertight
Long Description	Rated watertight for 1,500 psi high-pressure hosedown, Pass and Seymour plugs and connectors feature multiple seals to ensure protection against the environment. Constructed of a sturdy rubber body, which makes them impact- and chemical-resistant, they have nickel-plated blades and contacts for superior corrosion resistance.
Product Type	STR Blade IP67 Conn 15A 125V 5-15R
Special Features	Quick drive assembly screws, floating blades, rubber body construction, multiple ring seals



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

6112 42nd Street
79407-0000, TX Lubbock
Phone: 806-698-6329
Fax: 806-698-6805

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007114164
Manufacturers Part Number	15W-47
UPC	785007114164

Taxonomies, Classifications, and Categories

Category Description	Industrial cord connectors
Type	CONNECTOR

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.44

Uses, Certifications, and Standards

Application	Commercial
nema rating	5-15P
standard	UL, CSA, UL 498