

# Specifications



## Eaton 16204-3

Eaton Bussmann series power splicer block, 600 Vac, 600 Vdc, 175 A, Three-pole, SCCR: 200 kA, Black, Molded Thermoplastic Base, Tin-plated aluminum connector

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series power splicer block
<b>CATALOG NUMBER</b>	16204-3
<b>UPC</b>	051712148658
<b>PRODUCT LENGTH/DEPTH</b>	3 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	0.414 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Contact factory RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer



Powering Business Worldwide

## Electrical rating

<b>AMPERAGE RATING</b>	175A
<b>SHORT-CIRCUIT RATING</b>	SCCR: 200 kAIC
<b>VOLTAGE RATING</b>	600 Vac, 600 Vdc

## General information

<b>CONNECTION</b>	Splicer
-------------------	---------

## Physical details

<b>COLOR</b>	Black
<b>MATERIAL</b>	Molded thermoplastic base, tin plated aluminum connector
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Power splicer block

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a> <a href="#">16204-3~BUSS POWER BLOCK</a>
CERTIFICATION REPORTS	<a href="#">Eaton Bussmann EU Declaration of conformity 93-68-EEC2414</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 16204-3</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.

# Specifications



## Eaton 16204-3

Eaton Bussmann series power splicer block, 600 Vac, 600 Vdc, 175 A, Three-pole, SCCR: 200 kA, Black, Molded Thermoplastic Base, Tin-plated aluminum connector

### General specifications

<b>PRODUCT NAME</b>	Eaton Bussmann series power splicer block
<b>CATALOG NUMBER</b>	16204-3
<b>UPC</b>	051712148658
<b>PRODUCT LENGTH/DEPTH</b>	3 in
<b>PRODUCT HEIGHT</b>	1 in
<b>PRODUCT WIDTH</b>	3 in
<b>PRODUCT WEIGHT</b>	0.414 lb
<b>WARRANTY</b>	Not Applicable
<b>COMPLIANCES</b>	Contact factory RoHS Compliant
<b>CERTIFICATIONS</b>	Contact Manufacturer



Powering Business Worldwide

## Electrical rating

<b>AMPERAGE RATING</b>	175A
<b>SHORT-CIRCUIT RATING</b>	SCCR: 200 kAIC
<b>VOLTAGE RATING</b>	600 Vac, 600 Vdc

## General information

<b>CONNECTION</b>	Splicer
-------------------	---------

## Physical details

<b>COLOR</b>	Black
<b>MATERIAL</b>	Molded thermoplastic base, tin plated aluminum connector
<b>NUMBER OF POLES</b>	Three-pole
<b>TYPE</b>	Power splicer block

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a> <a href="#">16204-3~BUSS POWER BLOCK</a>
CERTIFICATION REPORTS	<a href="#">Eaton Bussmann EU Declaration of conformity 93-68-EEC2414</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - 16204-3</a>

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

Follow us on social media to get the latest product and support information.



© 2025 Eaton. All Rights Reserved.