



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818



161 *Discontinued* 250W Bulb Heater W/O Vent

Broan/Nutone LLC

Catalog Number	161
Manufacturer	Broan/Nutone LLC
Description	Heater. Same As Model 162 Except Without Ventilator. Not Type Ic.
Weight per unit	5.3 (lbs/each)
Product Category	Combination Fans, Lights & Hea

Features

dimensions	Housing: 8-3/8 IN Length X 8-1/8 IN Width X 6 IN Height, Grille: 10-1/4 IN Length X 10-1/4 IN Width X 5/8 IN Height
Voltage Rating	120
Wattage	250

Material, Color, and Finish

Housing Material	Steel
------------------	-------

Descriptions

Description	*DISCONTINUED* 250W BULB HEATER W/O VENT
Long Description	Heater. Same as Model 162 except without ventilator. Not Type IC.
Product Type	One-Bulb Heater, Broan, 250 WTT, 120 V, Ceil, STL HSG, 2.1 Amp
Special Features	Features: UL Listed For 75 DEG C Wiring (Retrofits); Adjustable Mounting Brackets With Keyhole Slots That Span Up To 24.000 IN; Use 250-Watt BR40 Size Infrared Bulbs (Not Included); Use With Broan Model 68 W Or 68 V Two-Function Control (Available Separately); White-White Polymeric Grille; Sturdy Steel Housing; Housing Can Be Adjusted Vertically After Ceiling Is Finished; Finish: White Grille; Amperage Rating: 2.1 AMP; Housing Size: 8-1/8 IN Length X 8-3/8 IN Width X 6 IN Height; Grille Material: Polymeric

Manufacturer Information

Brand	BROAN
GTIN	00026715002634
Model	161
UPC	026715002634

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	One-Bulb Infrared Heater



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

13405 Stemmons Frwy
75234-0000, TX Farmers Branch
Phone: 972-206-0016
Fax: 972-352-2818

Availability

Status Inactive

Packaging

Carton 1

Weight Per each 5.3

Uses, Certifications, and Standards

Application For Energy-Saving Warmth And Instant Comfort In The Bathroom

Mounting CEILING

standard UL