

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



165BL4A Temflex Vinyl Electrical Tape, BL, 3/4" X 60' *Minnesota Mining (3M)*

Minnesota Mining (3M)		
Catalog Number	165BL4A	
Manufacturer	Minnesota Mining (3M)	
Description	3M™ Temflex™ Vinyl Electrical Tape 165, Blue, 3/4 In X 60 FT (19	
	MM X 18 M), 100 Rolls/Case	
Weight per unit		
Product Category	Tools & Testers	
Features		
Adhesive Type	Rubber	
Dielectric Strength	1000	
Elongation at Break	2	
Voltage Rating	600	
Material, Color, and Finish		
Backing Material	Polyvinyl Chloride PVC	
Dimensions and Weight		
Thickness	6	
Descriptions Description	TEMFLEX VINYL ELECTRICAL TAPE, BL, 3/4" X 60'	
extra long description	3M 7100169429 3M™ Temflex™ Vinyl E	
Features	3M™ Temflex™ Vinyl Electrical Tape 165 is a 6-mil thick,	
reatures	multi-purpose vinyl insulating tape available in 10 colors. It is	
	designed to perform in ambient temperatures up to 194°F (90°C)	
	The tape is conformable for cold weather application down to	
	32°F (0°C). It has excellent resistance to abrasion, moisture,	
	alkalies, acid, copper corrosion and varying weather conditions.	
	The combination of an elastic PVC backing and pressure-sensitive	
	rubber-based adhesive provides electrical and mechanical	
	protection w	
Long Description	3M™ Temflex™ Vinyl Electrical Tape 165, Blue, 3/4 in x 60 ft (19	
	mm x 18 m), 100 Rolls/Case	
Product Type	3M™ Temflex™ Vinyl Electrical Tape 165	
Manufacturer Information		
Brand	Temflex	
GTIN	00076308925697	
Manufacturers Part Number	165BL4A	
UPC	076308925697	

Taxonomies, Classifications, and Categories

Category Description TAPE



ELLIOTT ELECTRIC SUPPLY 2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Packaging		
Carton	1	
Package	10	
Uses, Certifications, and Stand	dards	
Application	Insulation	