




CAT #	A	B
1491	1.400	.860
1492	2.035	1.060
1493	2.350	1.330



CAT #	A	B
1511	1.045	.860
1512	1.105	1.060
1513	1.220	1.330



CAT #	A	B
1611	1.045	.860
1612	1.105	1.060
1613	1.220	1.330



ENT COUPLINGS

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	PVC WT/ CASE
1491	82528	1/2"	—	200	9
1492	82529	3/4"	—	200	16
1493	82530	1"	—	100	14



ENT TERMINAL ADAPTERS THREADED

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1511	82531	1/2"	—	200	.40
1512	82532	3/4"	—	200	.40
1513	82533	1"	—	100	.40



ENT TERMINAL ADAPTERS SNAP-IN

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1611	82534	1/2"	—	200	.40
1612	82535	3/4"	—	200	.40
1613	82536	1"	—	100	.40




ENT CONDUIT COILS


• COIL

TOPAZ CAT #	UPC#	SIZE	FEET PER COIL	UNIT CTN	FEET PER PACK	WT/ FOOT
1621	82537	1/2"	200	—	400	.12
1622	82538	3/4"	100	—	200	.14
1623	82539	1"	100	—	100	.17


• REEL

TOPAZ CAT #	UPC#	SIZE	FEET PER REEL	UNIT CTN	FEET PER PACK	WT/ FOOT
1621R	83682	1/2"	1500	—	1500	.12
1622R	83680	3/4"	1000	—	1000	.14
1623R	83681	1"	750	—	750	.17







CAT #	A	B
1491	1.400	.860
1492	2.035	1.060
1493	2.350	1.330



CAT #	A	B
1511	1.045	.860
1512	1.105	1.060
1513	1.220	1.330



CAT #	A	B
1611	1.045	.860
1612	1.105	1.060
1613	1.220	1.330



ENT COUPLINGS

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	PVC WT/ CASE
1491	82528	1/2"	—	200	9
1492	82529	3/4"	—	200	16
1493	82530	1"	—	100	14



ENT TERMINAL ADAPTERS THREADED

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1511	82531	1/2"	—	200	.40
1512	82532	3/4"	—	200	.40
1513	82533	1"	—	100	.40



ENT TERMINAL ADAPTERS SNAP-IN

TOPAZ CAT #	UPC#	SIZE	UNIT CTN	SHIP CASE	WT/ CASE
1611	82534	1/2"	—	200	.40
1612	82535	3/4"	—	200	.40
1613	82536	1"	—	100	.40



ENT CONDUIT COILS

• COIL

TOPAZ CAT #	UPC#	SIZE	FEET PER COIL	UNIT CTN	FEET PER PACK	WT/ FOOT
1621	82537	1/2"	200	—	400	.12
1622	82538	3/4"	100	—	200	.14
1623	82539	1"	100	—	100	.17

• REEL

TOPAZ CAT #	UPC#	SIZE	FEET PER REEL	UNIT CTN	FEET PER PACK	WT/ FOOT
1621R	83682	1/2"	1500	—	1500	.12
1622R	83680	3/4"	1000	—	1000	.14
1623R	83681	1"	750	—	750	.17

