



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253



198 4000W Wall Heater

Broan/Nutone LLC

Catalog Number	198
Manufacturer	Broan/Nutone LLC
Description	Wall Heater, 2000/4000W 240VAC, 1500/3000W 208VAC. White Painted Grille.
Weight per unit	21.7 (lbs/each)
Product Category	Wall Heaters

Features

dimensions	Housing: 14-1/4 IN Length X 3-3/4 IN Width X 18 IN Height, Grille: 16-3/8 IN Length X 1-1/4 IN Width X 20-1/4 IN Height
Voltage Rating	240
Wattage	2,000/4,000

Material, Color, and Finish

Housing Material	22-Gauge Steel
------------------	----------------

Descriptions

Description	4000W WALL HEATER
Long Description	Wall Heater, 2000/4000W 240VAC, 1500/3000W 208VAC. White painted grille.
Product Type	Wall Heater, Broan, High-Capacity, 4000/2000 WTT, 240 Vac, 16.7/8
Special Features	Features: Factory Wired For 4000 W At 240 VAC - Easily Converts To Half-Wattage; 100 PCT Efficient Heating Element; Steel-Sheathed, Plate-Finned, Heavy-Duty Enclosed Heating Element Provides Heat Quickly And Quietly; Adjustable, Built-In Heavy-Duty Disc-Type Thermostat, Thermostat Security Cover Included, Can Be Operated By Built-In Adjustable Thermostat Or Optional Wall-Mount Thermostat; Manual Reset Overload Protection; Internal Fan Delay Prevents Cold Air Delivery; Heavy-Duty, One-Piece Steel Grille Lou

Manufacturer Information

Brand	BROAN
GTIN	00026715022670
Model	198
UPC	026715022670

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	High-Capacity



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

802 West Main
75652-4459, TX Henderson
Phone: 903-657-1517
Fax: 903-657-0253

Packaging

Carton 1

Weight Per each 21.7

Uses, Certifications, and Standards

Application For Lobbies, Entrance Ways, Vestibules Or Any Area Requiring
High Wattage Heating

Mounting Wall Stud, Recess/Surface

standard UL