

# Eaton 1MP3206RRL

Catalog Number: 1MP3206RRL

Eaton meter pack, Socket amperage: 200A, Amperage rating: 200A, Aluminum, Bus rating: 600A, No bypass, Indoor/outdoor, Up to 100 KAIC, 3 Sockets, Five-jaw, Single-phase in/single-phase out, Ringless, 120/240 Vac



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton meter pack	1MP3206RRL
<b>UPC</b>	<b>Product Length/Depth</b>
786849052539	7.01 in
<b>Product Height</b>	<b>Product Width</b>
64.56 in	25.5 in
<b>Product Weight</b>	<b>Warranty</b>
116 lb	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>Certifications</b>	
UL Listed	

## defaultTaxonomyAttributeLabel

### Utility approvals

ME : Central Maine Power  
GA : Georgia Power  
KS : Kansas City Power and Light (KCPL) / Westar Energy  
MO : Kansas City Power and Light (KCPL) / Westar Energy  
TN : Middle Tennessee EMC  
NM : Public Service Company of New Mexico (PNM)  
FL : Tallahassee City Electric  
IN : Indiana Michigan Power (IMP) (AEP East)  
MI : Indiana Michigan Power (IMP) (AEP East)  
OH : AEP Ohio (AEP East)  
TN : Appalachian Power (AEP East)  
VA : Appalachian Power (AEP East)  
WV : Appalachian Power (AEP East)

### Interrupt rating

Up to 100 KAIC

### Secondary circuit breaker

CCV2\_X, CCVH2\_X, CVS2\_XMM, CV2\_XMM, CVH2\_XMM

### Enclosure

Indoor/outdoor

### Voltage rating

120/240 V

### Amperage Rating

200A

### Bus material

Aluminum

### Bus Rating

600 A

### Bypass

None

### Number of jaws

Five-jaw

### Number of sockets

3

### Security

Ringless

### Socket amperage

## Resources

### Catalogs

Eaton's Volume 1—Residential and Light Commercial

### Drawings

Dimensional Drawing - METER PACKS, DIMENSIONS, 200A, 3 METER DEVICE

### Specifications and datasheets

Eaton Specification Sheet - 1MP3206RRL

### Warranty guides

Selling Policy 25-000 - Distribution and Control Products and Services



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)