



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2016104 Encl NM4 Enclosure *Cooper B-Line/Cable Tray*

|                  |                                                                                                                                                                                                                  |
|------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number   | 2016104                                                                                                                                                                                                          |
| Manufacturer     | Cooper B-Line/Cable Tray                                                                                                                                                                                         |
| Description      | Eaton B-Line Series Wall Mounted Panel Enclosure, 20" Height, 6" Length, 16" Width, Nema 4, Hinged Cover, 4 Enclosure, Medium Single Door, External Mounting Feet, Carbon Steel, Seamless Poured In-Place Gasket |
| Weight per unit  | 28.3 (lbs/each)                                                                                                                                                                                                  |
| Product Category | Nema Types 4 & 12 Metallic Enc                                                                                                                                                                                   |

### Features

|               |                                     |
|---------------|-------------------------------------|
| dimensions    | 6.0000 IN X 16.0000 IN X 20.0000 IN |
| Mounting Type | Wall                                |

### Material, Color, and Finish

|       |      |
|-------|------|
| Color | Gray |
|-------|------|

### Dimensions and Weight

|      |                                                   |
|------|---------------------------------------------------|
| Size | 16.00 In Width X 10.00 In Depth X 20.00 In Height |
|------|---------------------------------------------------|

### Descriptions

|                        |                                                                                                                                                                                                                  |
|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Description            | ENCL NM4 ENCLOSURE                                                                                                                                                                                               |
| extra long description | B-LINE 201610-4 TYPE 4 SGL-DOOR ENC                                                                                                                                                                              |
| Features               | Eaton's B-Line series wall mounted panel enclosures provide reliable environmental protection and are used to house electrical controls and instruments.                                                         |
| Long Description       | Eaton B-Line series wall mounted panel enclosure, 20" height, 6" length, 16" width, NEMA 4, Hinged cover, 4 enclosure, Medium single door, External mounting feet, Carbon steel, Seamless poured in-place gasket |
| Product Type           | Type 4 SGL-Door Enc, 20X16X10                                                                                                                                                                                    |
| Special Features       | Stainless door clamps                                                                                                                                                                                            |

### Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | Eaton          |
| GTIN                      | 00782051812206 |
| Manufacturers Part Number | 201610-4       |
| UPC                       | 782051812206   |

### Taxonomies, Classifications, and Categories

|                      |                              |
|----------------------|------------------------------|
| Category Description | STEEL JUNCTION BOXES         |
| Type                 | Wall mounted panel enclosure |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

|                 |        |
|-----------------|--------|
| Carton          | 1      |
| Weight Per each | 28.265 |

## Uses, Certifications, and Standards

|             |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
|-------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | Utility - Substations, Utility Transmission and Distribution<br>Commercial / Institutional Buildings / Structures - Critical Power<br>Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other<br>Other IT and Datacom - IT and Datacomm - Other<br>Commercial / Institutional Buildings / Structures - Commercial/Inst Bldg<br>Structures - Aftermarket<br>Commercial / Institutional Buildings / Structures - Power Distribution and Controls<br>Generation - Renewable Energy - Alternative Energy |
| Mounting    | EXTERNAL FEET, WALL                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                        |
| nema rating | 4                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                          |
| standard    | NEMA,UL 50,CSA C22.2.                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                      |