



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **2097TRWR Radiant Self Test TR WR Gfci 20A 125V B** *Pass & Seymour/Legrand*

Catalog Number	2097TRWR
Manufacturer	Pass & Seymour/Legrand
Description	Gfci Receptacles From The Radiant Registered Collection Self-Test Automatically Every Three Seconds to Ensure Reliable Protection From Shock Due to Ground Fault Occurrences. Meeting National Electrical Code Requirements For Ground Fault Protection, Gfci Receptacles Make It Easier to Recognize and Fix Trips Right Where They Happen – No More Confusion At The Breaker Box. Also Including Tamper and Weather* Resistance, This Model Was Designed For Use In Outdoor Spaces. Maximize Safety, In Style, With Gfci Prot
Weight per unit	0.2750 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

### **Features**

actuator	Control Circuit
amperage rating	20
connection	Back and side wire
indoor/outdoor	Outdoor
interrupt rating	4 to 6 mA
Material	Thermoplastic
Mounting Type	Box
Number of Gangs	1.0
Outlet Type	Tamper-Resistant, Self-Test, Weather-Resistant, GFCI
Poles	2
trip range	4 to 6 mA
Trip Type	.025 Second Nominal
Voltage Rating	125

### **Material, Color, and Finish**

Finish	Matte
--------	-------

### **Dimensions and Weight**

Height	4.2
Length	1.03
Width	1.73



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Description	RADIANT SELF TEST TR WR GFCI 20A 125V B
extra long description	P&S 2097TRWR RADIANT SELF TEST TR W
Long Description	GFCI receptacles from the radiant Registered Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Also including tamper and weather* resistance, this model was designed for use in outdoor spaces. Maximize safety, in style, with GFCI prot
Product Type	Radiant Self Test TR WR Gfci 20A 125V B
Special Features	Spec Grade, Weather Resistant

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007036053
Manufacturers Part Number	2097-TRWR
UPC	785007036053

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	10
Weight Per each	0.275

## Uses, Certifications, and Standards

Application	Commercial/Residential
environmental conditions	95% Humidity, UL 94 V2
Frequency Rating	60 Hz
nema rating	20A
Operating Temperature	-35°C to +66°C
standard	UL, cULus