



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



2134W Wallplate 1G Toggle Thermoset STD WH

Eaton Wiring Devices

Catalog Number	2134W
Manufacturer	Eaton Wiring Devices
Description	Wallplate 1G Toggle Thermoset STD WH
Weight per unit	0.0600 (lbs/each)
Product Category	Wiring Devices & Data/Telecom

Features

cutout	0.40 In Width X 0.93 In Height
gang	1 PH

Material, Color, and Finish

Color	WHITE
-------	-------

Dimensions and Weight

Size	Standard, 2.75 In Width X 4.50 In Height
Thickness	0.080 In

Descriptions

Construction	Warp Resistant
Description	1G SWITCH PLATE
Long Description	Wallplate 1G Toggle Thermoset Std WH
Product Type	Wallplate 1G Toggle Thermoset STD WH
Special Features	Standard Grade, Flush Fitting

Manufacturer Information

Brand	COOPER WIRING DEVICES
GTIN	00032664155604
Manufacturers Part Number	2134W-BOX
sub brand	ARROW HART
UPC	032664155604

Taxonomies, Classifications, and Categories

Category Description	RESIDENTIAL GRADE 1G PLATE
Type	(1) Toggle Switch

Packaging

Carton	25
Package	200
Weight Per each	0.06


Uses, Certifications, and Standards

Application	RESIDENTIAL
Mounting	4714


Standard size wallplates toggle switch

Product description


1-Gang, 2-Gang, 3-Gang, 4-Gang, 5-Gang, 6-Gang




1-Gang




2-Gang




3-Gang



4-Gang



5-Gang



6-Gang

Toggle switch wallplates

Gang	Material	Color suffix	Catalog no.		
1-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5134__	•	•
	Thermoset	A, B, LA, V, W	□ 2134__	•	•
	302/304 stainless steel	—	□ 93071	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93071__	•	•
	Brass	—	□ 94071	•	•
2-Gang	Nylon	A, B, BK, GY, LA, RD, V, W	□ 5139__	•	•
	Thermoset	A, B, LA, V, W	□ 2139__	•	•
	302/304 stainless steel	—	□ 93072	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93072__	•	•
	Brass	—	□ 94072	•	•
3-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5141__	•	•
	Thermoset	A, B, LA, V, W	□ 2141__	•	•
	302/304 stainless steel	—	□ 93073	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93073__	•	•
	Brass	—	□ 94073	•	•
4-Gang	Nylon	A, B, BK, GY, LA, V, W	□ 5154__	•	•
	Thermoset	A, B, LA, V, W	□ 2154__	•	•
	302/304 stainless steel	—	□ 93074	•	•
	CuVerro® antimicrobial copper	CU, CUR	□ 93074__	•	•
	Brass	—	□ 94074	•	•
5-Gang	Thermoset	A, B, LA, V, W	□ 2155__	•	•
	302/304 stainless steel	—	□ 93075	•	•
6-Gang	Thermoset	A, B, V, W	□ 2156__	•	•
	302/304 stainless steel	—	□ 93076	•	•

See additional CuVerro® wallplate information on K-22

Color ordering information:

For ordering devices, include Catalog no. followed by the Color suffix: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), RD (Red), V (Ivory), W (White), CU (White Bronze) CuVerro® ONLY, CUR (Rose) CuVerro® ONLY



Certification information: 2000, 4000, 5000, ST & PJ series wallplates are cULus Listed; 93000 series wallplates are UL Listed and CSA Certified; 94000 series are UL Listed and CSA certified; CuVerro® series wallplates are only UL Listed. **Specification information:** K-22

Compliances, specifications and availability are subject to change without notice.

Indicates NAFTA compliant - Page Q-30

RoHS compliant – Page Q-30