

Compact Polycarbonate Exit Signs Specification


LED Exit Signs 120 or 277 Voltage, Damp Location

Features and Benefits:

- Injection-molded thermoplastic ABS housing
- UL 94V-0 flame rating
- Innovative, snap-together design allows for fast installation
- Replaceable directional chevron inserts are easily removed and reinserted
- Letters 6" height with 3/4" stroke
- Single or double face configuration
- Universal mounting- wall, side, or ceiling
- Housing snaps to canopy with simple twist and locking tightly secure housing to canopy
- 120/277 VAC dual voltage operation
- Low energy consumption- only 2.0 W at 120v
- LED indicator light and push button test switch
- LEDs mounted on print circuit board
- LED lamps are operating in normal (AC input) and emergency (DC input) modes
- 24 hours recharge after 90 minute discharge
- Low voltage battery disconnection- preventing deep discharge damage to the battery
- Maintenance-Free, Ni-Cd battery provides an estimated service life of 10 years with an operating temperature range of 10C to 40C
- ETL Listed for damp location
- Meets NFPA 101, NEC, and UL924 approvals



Dimensions:



Warranties & Compliances:	Item#	Description	LED Color	Housing Color	AC/BBUP
	Ordering Information: 22742 22743	Red LED Exit Sign Universal AC Only WH Housing Red LED Exit Sign Universal Battery Backup WH Housing	Red Red	White White	AC BBUP
NFPA® NATIONAL FIRE PROTECTION ASSN.	22744 22745 22746 22747 22748 22749	Green LED Exit Sign Universal AC Only WH Housing Green LED Exit Sign Universal Battery Backup WH Housing Red LED Exit Sign Universal AC Only BLK Housing Red LED Exit Sign Universal Battery Backup BLK Housing Green LED Exit Sign Universal AC Only BLK Housing Green LED Exit Sign Universal Battery Backup BLK Housing	Green Green Red Red Green Green	White White Black Black Black Black	AC BBUP AC BBUP AC BBUP
Ni-Cd battery 5 YEAR WARRANTY	Accessories:	Wire Guard for Exit Sign			
Electronics 5 YEAR WARRANTY	207WGWH 207PS 207B3 207B2	White Wire Guard for Exit Sign Polycarbonate Shield for Exit Sign Replacement Battery Ni-Cd 3.6V 300mAh for 22745 & 22749 units Replacement Battery Ni-Cd 2.4V 300mAh for 22743 & 22747 units			
LED Strip 25 WARRANTY	29999 29999G 20704 CHEVRONPL	Red Diffuser Panel Green Diffuser Panel Replacement White Canopy Replacement White Chevron			





PARTNER OF THE YEAR