



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1315 2nd Street MAIP  
74361-0000, OK Pryor  
Phone: 918-803-0063  
Fax: 918-803-0064



## 24FP4740C 40W 2X4 Led Flat Panel 40K

*Cooper Lighting Solutions*

Catalog Number	24FP4740C
Manufacturer	Cooper Lighting Solutions
Description	2X4 Led Recessed Flat Panel, 4700 Lumen, 4000K, 80 Cri, 0-10V Continuous Dimming Driver
Weight per unit	25.8 (lbs/each)
Product Category	Led Recessed Architectural & S

### Features

amperage rating	0.15@277V A
Ballast Type	N/A IN
Lamp Type	INCANDESCENT LANDSCAPE LIGHT FIXTURE, ECLIPSE TYPE; ALUMINUM MATERIAL; 4.5 INCH W X 18.5 INCH H SIZE; TEXTURED ARCHITECTURAL BRONZE FINISH; UL (CANADA AND US), CSA, ETL (US) APPROVAL; 8 INCH IN-GROUND STAKE, 18 INCH STEM MOUNTING
Voltage Rating	120/277 VAC
Wattage	40.3W

### Dimensions and Weight

Height	50.438 in
Length	50.813 in
Width	3.125 in

### Descriptions

Description	40W 2X4 LED FLAT PANEL 40K
extra long description	ETNCL 24FP4740C 2X4 FANEL 4700L, 4
Long Description	2x4 LED recessed flat panel, 4700 Lumen, 4000K, 80 CRI, 0-10V continuous dimming driver
Product Type	2X4 Fpanel 4700L, 40K, 0-10V
Special Features	Ultra thin less than 2" height fits shallow plenums with room to spare

### Manufacturer Information

Brand	METALUX COMMERCIAL
GTIN	00080083801480
Manufacturers Part Number	24FP4740C
sub brand	Fpanel LED Panel Series
UPC	080083801480



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1315 2nd Street MAIP  
74361-0000, OK Pryor  
Phone: 918-803-0063  
Fax: 918-803-0064

## Taxonomies, Classifications, and Categories

Category Description ..... LED ARCHITECTURAL & SPECIFICATION LIGHTING  
Type ..... RECESSED

## Availability

Status ..... Inactive

## Packaging

Carton ..... 1  
Weight Per each ..... 25.79

## Uses, Certifications, and Standards

Application ..... lighting  
Mounting ..... Recessed