



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St  
70123-0000, LA Harahan  
Phone: 504-264-9995  
Fax: 504-264-5996



## 24FP4750C 40W 2X4 Led Flat Panel 50K

*Cooper Lighting Solutions*

Catalog Number	24FP4750C
Manufacturer	Cooper Lighting Solutions
Description	FP Series 2X4 Led Recessed Flat Panel, 4700 LM, 5000K, 80CRI, 0-10V Dimming Driver
Weight per unit	25.8 (lbs/each)
Product Category	Led Surface General Purpose Li

### Features

amperage rating	0.145@277V A
Lamp Type	INCANDESCENT LANDSCAPE LIGHT FIXTURE, ECLIPSE TYPE; ALUMINUM MATERIAL; 4.5 INCH W X 18.5 INCH H SIZE; TEXTURED ARCHITECTURAL BRONZE FINISH; UL (CANADA AND US), CSA, ETL (US) APPROVAL; 8 INCH IN-GROUND STAKE, 18 INCH STEM MOUNTING
Voltage Rating	120/277 VAC
Wattage	40 W

### Dimensions and Weight

Height	50.438 in
Length	50.813 in
Width	3.125 in

### Descriptions

Description	40W 2X4 LED FLAT PANEL 50K
extra long description	ETNCL 24FP4750C 2X4 FPANEL 4700L, 5
Long Description	FP Series 2x4 LED recessed flat panel, 4700 LM, 5000K, 80CRI, 0-10V dimming driver
Product Type	2X4 Fpanel 4700L, 50K, 0-10V
Special Features	Ultra thin 1.75" height fits shallow plenums with room to spare

### Manufacturer Information

Brand	METALUX COMMERCIAL
GTIN	00080083801503
Manufacturers Part Number	24FP4750C
sub brand	Fpanel LED Panel Series
UPC	080083801503

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St  
70123-0000, LA Harahan  
Phone: 504-264-9995  
Fax: 504-264-5996

## Availability

Status ..... Inactive .....

## Packaging

Carton ..... 1 .....

Weight Per each ..... 25.79 .....

## Uses, Certifications, and Standards

Application ..... lighting .....

Mounting ..... Recessed .....