



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 24SRLD248CUNVL84 2X4 Led Layin 40K 4800LM

*Cooper Lighting Solutions*

|                  |                                                                                                |
|------------------|------------------------------------------------------------------------------------------------|
| Catalog Number   | 24SRLD248CUNVL84                                                                               |
| Manufacturer     | Cooper Lighting Solutions                                                                      |
| Description      | Led, 2'X4' Skyridge, Wavestream, 4800 Lumens, 85 Cri, 4000K, Unv 0-10V Dimming Driver, Curved. |
| Weight per unit  | 28.0 (lbs/each)                                                                                |
| Product Category | Lighting                                                                                       |

### Features

|                 |               |
|-----------------|---------------|
| amperage rating | 0.138 at 277V |
| Ballast Type    | N/A           |
| Lamp Type       | LED           |
| Material        | Aluminum      |
| Number of Lamps | 1             |
| Socket Type     | N/A           |
| Voltage Rating  | 120/277V      |

### Material, Color, and Finish

|       |         |
|-------|---------|
| Style | (blank) |
|-------|---------|

### Descriptions

|                        |                                                                                                |
|------------------------|------------------------------------------------------------------------------------------------|
| Description            | 2X4 LED LAYIN 40K 4800LM                                                                       |
| extra long description | CLS 24SR-LD2-48-C-UNV-L840-CD1-U SR                                                            |
| Long Description       | LED, 2'x4' SkyRidge, WaveStream, 4800 Lumens, 85 CRI, 4000K, UNV 0-10V Dimming Driver, Curved. |
| Product Type           | SR Led 2X4, 4800LM, 4K, Unv 0-10 Dim DRV                                                       |
| Special Features       | Available in 1' x 2', 1' x 4', 2' x 2' and 2' x 4' recessed versions                           |

### Manufacturer Information

|                           |                              |
|---------------------------|------------------------------|
| Brand                     | METALUX                      |
| GTIN                      | 00080083752485               |
| Manufacturers Part Number | 24SR-LD2-48-C-UNV-L840-CD1-U |
| UPC                       | 080083752485                 |

### Taxonomies, Classifications, and Categories

|                      |                                            |
|----------------------|--------------------------------------------|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type                 | Recessed Static                            |

### Availability

|        |          |
|--------|----------|
| Status | Inactive |
|--------|----------|

### Packaging

|                 |    |
|-----------------|----|
| Carton          | 1  |
| Weight Per each | 28 |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Uses, Certifications, and Standards

|             |                                                                                                                                                                       |
|-------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Application | lighting                                                                                                                                                              |
| Mounting    | Recessed                                                                                                                                                              |
| standard    | UL Recognized;cULus Listed;LM79/LM80 Compliant;DLC<br>Qualified;IC Rated;RoHS Compliant;Damp Locations Listed;NOM<br>Certified;25 Degree C Ambient Temperature Rating |