



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



252DCI2 1" Emt Insulated Concrete Tight Connector *Bridgeport Fittings*

Catalog Number	252DCI2
Manufacturer	Bridgeport Fittings
Description	Emt Concrete Tight Connector, 1 In Trade Size, Die-Cast Zinc Material, Insulated, 15/16 In Length, 1-11/16 In Diameter, +105 °C Operating Temperature, 0.1590 LB/Ea
Weight per unit	0.1590 (lbs/each)
Product Category	Die Cast Insulated Straight CO

Features

Connector Type	Compression
media	Yes
Trade Size	1 PH

Material, Color, and Finish

Finish	Ball burnished, mirror smooth
--------	-------------------------------

Dimensions and Weight

Size	1 PH
------	------

Descriptions

Description	1" EMT INSULATED CONCRETE TIGHT CONNECTOR
-------------	---

Manufacturer Information

Brand	Bridgeport
GTIN	00781747162526
UPC	781747162526

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	CONNECTOR

Packaging


Carton	1
Package	15
Weight Per each	0.159

Uses, Certifications, and Standards

standard	UL, CSA
Temperature Rating	105 W

Connectors - Zinc

Images



Application

Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105°C. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Product Information

Material: Zinc Die Cast
Finish: Ball burnished, mirror smooth

Certifications & Codes:

CSA File Number:	LR39354
Federal Specification Number:	A-A-50553
NEMA Standard:	FB-1
UL File Number:	E24001
UL Standard:	UL-514B
UNSPSC:	39121434

[Download Photo Image](#) [Download Dimensional Image](#)

Dimension A in Inches: 9/16
Dimension B in Inches: 15/16
Dimension C in Inches: 1-11/16

Catalog ID: 252-DC12

UPC Number: 781747162526

Description: Connector, Compression, Zinc Die Cast, 105°C Insulated Throat, Size 1 Inch

Application: Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105°C. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Trade Size: 1"

Country of Manufacture: USA

Std Pkg Qty: 150

Unit Qty: 15