



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3804 South Street
75964-7263, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



254DCI2 1-1/2" Emt Insulated Concrete Tight Connector *Bridgeport Fittings*

Catalog Number	254DCI2
Manufacturer	Bridgeport Fittings
Description	
Weight per unit	0.5400 (lbs/each)
Product Category	Die Cast Insulated Straight CO

Features

Connector Type	Compression
Material	ZINC DIE CAST
media	Yes
Trade Size	1-1/2 IN Rating

Material, Color, and Finish

Finish	Ball burnished, mirror smooth
--------	-------------------------------

Dimensions and Weight

Size	1 1/2 IN
------	----------

Descriptions

Description	1-1/2" EMT INSULATED CONCRETE TIGHT CONNECTOR
Product Type	1-1/2" Comp. Conn. Ins. Zinc
Special Features	Concrete-Tight

Manufacturer Information

Brand	Bridgeport
GTIN	00781747162540
Manufacturers Part Number	254-DCI2
UPC	781747162540

Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	CONNECTOR

Packaging



Carton	10
Package	40
Weight Per each	0.54

Uses, Certifications, and Standards

Application	Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105degree C.
standard	UL, CSA
Temperature Rating	105 W

Connectors - Zinc

Images



Application

Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105°C. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Product Information

Material: Zinc Die Cast

Finish: Ball burnished, mirror smooth

Certifications & Codes:

CSA File Number: LR39354

Federal Specification Number: A-A-50553

NEMA Standard: FB-1

UL File Number: E24001

UL Standard: UL-514B

UNSPSC: 39121434

[Download Photo Image](#)

[Download Dimensional Image](#)

Dimension A in Inches: 5/8

Dimension B in Inches: 1-5/16

Dimension C in Inches: 2-7/16

Catalog ID: 254-DC12

UPC Number: 781747162540

Description: Connector, Compression, Zinc Die Cast, 105 Degree C Insulated Throat, Size 1 1/2 Inch

Application: Used to join steel EMT to box or enclosure. Concrete-tight. 1/2" thru 2" suitable for use with Steel or Aluminum EMT. Insulator rated 105°C. CSA Listed Raintight/For Use in Wet Locations in Canada Only

Trade Size: 1-1/2"

Country of Manufacture: USA

Std Pkg Qty: 40

Unit Qty: 10