



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## 2623I SW Dec 3W 20A 120/277V Grounded I

*Pass & Seymour/Legrand*

Catalog Number	2623I
Manufacturer	Pass & Seymour/Legrand
Description	3-Way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Weight per unit	0.2200 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Fluorescent, Incandescent, Halogen, LED, Universal, CFL, Xenon
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	3-way
Switch Type	Paddle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	3
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	4.25"
------	-------

### Descriptions

Description	SW DEC 3W 20A 120/277V GROUNDED I
extra long description	P&S 2623I SW DEC 3W 20A 120/277V GR
Features	Decorator Style
Long Description	3-way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Product Type	SW Dec 3W 20A 120/277V Grounded I
Special Features	Impact resistant polycarb back body & frame, cushioned thermoplastic paddle , unique single rocking butterfly contact



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007539530
Manufacturers Part Number	2623-I
UPC	785007539530

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Decorator, Switch

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.22

## Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL CULUS, CSA, UL, UL 20