



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1035 S. Graham St.
76401-0000, TX Stephenville
Phone: 254-965-8083
Fax: 254-968-2662



25DTPE10 Tele-Power Express Pole (2) 5'

Wiremold/Legrand

Catalog Number	25DTPE10
Manufacturer	Wiremold/Legrand
Description	<P>Two Sections Of A Two-Compartment (Power and Communication) Pole (5'4"" (1.626M) Base + 5' (1.524M) Extender) Assembles to Form A 10' 4"" (3.148M) Pole. Nominal Material Thickness .040"" (1.0MM). Ivory or Gray Boot Base. Factory Wired With Fed-Spec General Grade 20A 125V Duplex Style Receptacles. An 8"" (203MM) Cover At Top Front (Power Side) Of Pole Is Removable For Making Power Wiring Connections. Kos Provided In Removable Cover For RJ11/RJ45 and Modular Furniture Communication Connectors. Mounting Ha
Weight per unit	22.0 (lbs/each)
Product Category	Telephone/Power Poles

Features

cutout	Receptacle, Data, Keystone, A/V
Material	Steel
Number of Channels	2.0

Material, Color, and Finish

Color	Ivory
-------	-------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1035 S. Graham St.
76401-0000, TX Stephenville
Phone: 254-965-8083
Fax: 254-968-2662

Descriptions

Description	TELE-POWER EXPRESS POLE (2) 5'
extra long description	WM 25DTP-E10 TELE-POWER EXPRESS POL
Features	<p>Two sections of a two-compartment (power and communication) pole (5'4" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" (203mm) cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting ha
Long Description	<p>Two sections of a two-compartment (power and communication) pole (5'4" (1.626m) base + 5' (1.524m) extender) assembles to form a 10' 4" (3.148m) pole. Nominal material thickness .040" (1.0mm). Ivory or gray boot base. Factory wired with fed-spec general grade 20A 125V duplex style receptacles. An 8" (203mm) cover at top front (power side) of pole is removable for making power wiring connections. KOs provided in removable cover for RJ11/RJ45 and modular furniture communication connectors. Mounting ha
Product Type	Tele-Power Express Pole (2)5FT
Special Features	Bring power, data, and A/V services into open spaceenvironments quickly & easily. Custom capabilities. On-site configurability. A/V Compatibility. Datacom connectivity options.

Manufacturer Information

Brand	WIREMOLD
GTIN	00786776172539
Manufacturers Part Number	25DTP-E10
UPC	786776172539

Taxonomies, Classifications, and Categories

Category Description	Panduit & Wiremold Metallic & Non-Metallic Raceways
Type	Pole

Packaging

Carton	1
Weight Per each	22

Uses, Certifications, and Standards

standard	ROHS, CULUS, cULus Listed, Multioutlet Assemblies: File E15191, E178348
----------	---