



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



25W47 Locking IP67 Conn 15A 125V L5-15R

Pass & Seymour/Legrand

| | |
|------------------|--|
| Catalog Number | 25W47 |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Locking Watertight Connector, 15AMP 125VOLT, Nema Configuration L5-15, Multipoint Sealing System Provides Environmental Protection Of Nema 4, 4X, 6, 6P, and IP67 Rated. |
| Weight per unit | 0.4400 (lbs/each) |
| Product Category | Plugs, Connectors, Inlets, Out |

Features

| | |
|-----------------|-------------|
| amperage rating | 15 |
| indoor/outdoor | Both |
| Material | Rubber |
| Number of Wires | 3.0 |
| Poles | 2 |
| Voltage | 125.0 V |
| Voltage Rating | 125 |
| Wire Size | 18 - 10 AWG |

Material, Color, and Finish

| | |
|-------|--------|
| Color | Yellow |
|-------|--------|

Dimensions and Weight

| | |
|------|----|
| Size | 4" |
|------|----|

Descriptions

| | |
|------------------------|--|
| Description | LOCKING IP67 CONN 15A 125V L5-15R |
| extra long description | P&S 25W47 LOCKING IP67 CONN 15A 125 |
| Features | Watertight |
| Long Description | Locking Watertight Connector, 15amp 125volt, NEMA Configuration L5-15, multipoint sealing system provides environmental protection of NEMA 4, 4X, 6, 6P, and IP67 rated. |
| Product Type | Locking IP67 Conn 15A 125V L5-15R |
| Special Features | Watertight, rubber body construction, closure cap, nickel plated blades, multiple seals between plug/connector |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007114249 |
| Manufacturers Part Number | 25W-47 |
| UPC | 785007114249 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|---|
| Category Description | NEMA RATED TURNLOK PLUGS, CONNECTORS, & RECEPTICLES |
| Type | CONNECTOR |

Trade Size

| | |
|----------|------|
| Amperage | 15.0 |
|----------|------|

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 10 |
| Weight Per each | 0.44 |

Uses, Certifications, and Standards

| | |
|-------------|-----------------|
| Application | Commercial |
| nema rating | L5-15R |
| standard | UL, CSA, UL 498 |