



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St  
70123-0000, LA Harahan  
Phone: 504-264-9995  
Fax: 504-264-5996



## 2621 Deco SWTCH B&S-W 1P 20A 120/277V Grounded BN

*Pass & Seymour/Legrand*

Catalog Number	2621
Manufacturer	Pass & Seymour/Legrand
Description	Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Weight per unit	0.1850 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	Halogen, Universal, LED, Xenon, CFL, Fluorescent, Incandescent
Material	Thermoplastic
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	1
Switch Type	Paddle
throw type	Single Throw
Voltage	120/277 V
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	1
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	4.25"
------	-------

### Descriptions

Description	DECO SWTCH B&S-W 1P 20A 120/277V GROUNDED BN
extra long description	P&S 2621 SW DEC 1P 20A 120/277V GRO
Features	Decorator Style
Long Description	Single-Pole, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Product Type	SW Dec 1P 20A 120/277V Grounded BN
Special Features	Impact resistant polycarb back body & frame, cushioned thermoplastic paddle , unique single rocking butterfly contact



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

221 Hord St  
70123-0000, LA Harahan  
Phone: 504-264-9995  
Fax: 504-264-5996

## Manufacturer Information

Brand	Pass & Seymour/Legrand
GTIN	00785007539301
Manufacturers Part Number	2621
UPC	785007539301

## Taxonomies, Classifications, and Categories

Category Description	Commercial switches
Type	Decorator, Switch

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.185

## Uses, Certifications, and Standards

Application	Industrial
Enclosure	Wall box
Mounting standard	WALL CSA, UL, CULUS, UL 20