



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299



## 2624I SW Dec 4W 20A 120/277V Grounded I

*Pass & Seymour/Legrand*

Catalog Number	2624I
Manufacturer	Pass & Seymour/Legrand
Description	4-Way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Weight per unit	0.2540 (lbs/each)
Product Category	Gen Purpose Switches

### Features

amperage rating	20
Contact Rating	20Amp, 120/277Vac
indoor/outdoor	Indoor
insulation	Bare
Load Rating	20 A @ 120/277 VAC
Load Type	LED, Halogen, CFL, Fluorescent, Xenon, Incandescent, Universal
Material	Thermoplastic
media	Yes
Mounting Type	Wall Box
Number of Gangs	1
Number of Switches	1.0
Poles	4-Way
Switch Type	Paddle
throw type	Double Throw
Voltage	120 VAC, 277 VAC
Voltage Rating	120/277
Wall Plate Included	NO
Wattage	4
Wire Size	#14 - #10 Awg

### Material, Color, and Finish

Finish	Matte
--------	-------

### Dimensions and Weight

Size	4.25"
------	-------

### Descriptions

Description	SW DEC 4W 20A 120/277V GROUNDED I
extra long description	P&S 2624I SW DEC 4W 20A 120/277V GR
Features	Decorator Style
Long Description	4-way, Back and Side-Wire, Decorator Switch, 20A, 120/277V.
Product Type	SW Dec 4W 20A 120/277V Grounded I
Special Features	Impact resistant polycarb back body & frame, cushioned thermoplastic paddle , unique single rocking butterfly contact



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

204 Lake Road  
76426-0000, TX Bridgeport  
Phone: 940-683-5740  
Fax: 940-683-5299

## Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007539639
Manufacturers Part Number	2624-I
UPC	785007539639

## Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Switch, Decorator

## Trade Size

Amperage	20.0
----------	------

## Packaging

Carton	1
Package	50
Weight Per each	0.254

## Uses, Certifications, and Standards

Application	Industrial
Mounting standard	WALL CSA, CULUS, UL 20