

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685



271920 M18 Fuel Hackzall (Tool Only) *Milwaukee Electric Tool*

271920
Milwaukee Electric Tool
The Milwaukee 2719 M18 Fuel™ Hackzall® Is The Fastest Cutting and Most Powerful One-Handed Reciprocating Saw. Utilizing A Powerstate Brushless Motor and A Best In Class 7/8 In. Stroke Length, The M18 Fuel™ Hackzall® Cuts Up to 50% Faster Than Competitors. The Compact, One-Handed Design Provides Superior Control and The Ability to Make Cuts In Tight Spaces. The Dual Gear Counter Balance Mechanism Provides Up to 4X Lower Vibration Than Traditional Reciprocating Saws, Resulting In Faster Cut-Starts In Metal A
4.6 (lbs/each)
Battery Driven Tools
18
Yes
0.875
Glass Filled Nylon
7
14
3.31



Carton Package

Weight Per each

ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr. 75964-0000, TX Nacogdoches Phone: 936-569-7941 Fax: 936-560-4685

Descriptions Description	M18 FUEL HACKZALL (TOOL ONLY)
extra long description	MILW 2719-20 Reciprocating Saw
Features	Milwaukee Tool is committed to protecting our users's investments by providing high performing, trade-focused solutions that are fully compatible with M18™ REDLITHIUM™ batteries. The M18™ system has over 200 performance-driven solutions, and growing!
Long Description	The Milwaukee 2719 M18 FUEL™ HACKZALL® is the fastest cutting and most powerful one-handed reciprocating saw. Utilizing a POWERSTATE brushless motor and a best in class 7/8 in. stroke length, the M18 FUEL™ HACKZALL® cuts up to 50% faster than competitors. The compact, one-handed design provides superior control and the ability to make cuts in tight spaces. The dual gear counter balance mechanism provides up to 4x lower vibration than traditional reciprocating saws, resulting in faster cut-starts in metal a
Product Type	Reciprocating Saw
Manufacturer Information	
Brand	Milwaukee®
GTIN	00045242502776
Manufacturers Part Number	2719-20
UPC	045242502776
Taxonomies, Classifications, and Category Description	DOLATED TO OLO
Packaging	

6 4.57