



- [Products](#)
- [Parts & Service](#)
- [Where to Buy](#)
- [Contact Us](#)
- [News & Events](#)
- [About Us](#)
- [Heavy Duty Club](#)
- [New Products](#)

Search



PRODUCTS

- ◆ [Tools](#)
- [Accessories](#)
- [Milwaukee Gear](#)
- [Catalog Request](#)


ALL TOOLS

- [Cordless Tools](#)
- [Cutoff Machines](#)
- [Diamond Coring Equipment](#)
- [Drain Cleaners](#)
- [Drills/Corded](#)
- [Generators](#)
- [Grinders](#)
- [Hammer-Drills/Corded](#)
- [Hammers/Demolition](#)
- [Hammers/Rotary](#)
- [Heat Guns](#)
- [Impact Wrenches/Corded](#)
- [Lifting Tools](#)
- [Magnetic Drilling Equipment](#)
- [Pneumatics](#)
- [Polishers](#)
- [Routers](#)
- [Sanders](#)
- [Saws/Corded](#)
- [Sawzall® Reciprocating Saws/Corded](#)
- [Screwdrivers/Corded](#)
- [Shears/Nibblers](#)
- [Tools by Trade](#)
- [Vacuum Cleaners](#)

Tools

◆ Tools ‣ [2691-22](#)

M18 2-TOOL COMBO KIT



- [PDF Owner's Manual](#)
- [PDF MSDS](#)
- [Related Articles](#)
- [PDF Service Parts List](#)
- [PDF Warranty](#)

[Zoom](#) [Where To Buy](#) [Email To A Friend](#)

FEATURES

- M18 ½" Compact Drill/Driver Delivers 400 In-lbs of Torque and is Only 4 lbs. and 7 ¾" Long
- M18 ¼" Hex Compact Impact with the Milwaukee 4-Pole Frameless Motor Delivers 1400 In-lbs. of torque

SPECIFICATIONS

- Voltage **18V**
- Battery **(2) 18V LITHIUM-ION Compact Battery Packs (48-11-1815)**
- Charger **30-Minute Charger**
- Number of Tools **2**
- Carrier **Carrying Case**
- Shipping Weight **14 lbs.**

INCLUDES

- **(2) 18V LITHIUM-ION Compact Battery Packs (48-11-1815)**
- **18V Charger (48-59-1801)**
- **Carrying Case**

The M18 2-Tool Combo Kit Combines Power Tools and Accessories in a Convenient Carrying Case at a Great Price.



RELATED PRODUCTS

- [18V XC High Capacity LITHIUM-ION Battery](#)



- [18V LITHIUM-ION Battery Charger](#)



- [18V Compact LITHIUM-ION Battery](#)



- [14 Piece Thunderbolt® Black and Bronze Drill Bit Set](#)

