



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000



26W76AM Turnlok Plug IP67 20A 3PH 480V L1620P Anti-Mic

Pass & Seymour/Legrand

Catalog Number	26W76AM
Manufacturer	Pass & Seymour/Legrand
Description	Steriguard Anti-Microbial Wiring Devices Provide Excellent Protection Against The Growth Of Microbes On All Surfaces. Independent Testing Proves The Ability Of These Devices to Inhibit The Growth Of Escherichia Coli, Gram (-) and Staphylococcus Aureus, Gram (+) Providing Long Lasting Benefits to Manufacturers Beyond Conventional Cleaning Methods. Rated Watertight For 1, 500 Psi High-Pressure
Weight per unit	0.5800 (lbs/each)
Product Category	Plugs, Connectors, Inlets, Out

Features

amperage rating	20
Cord Type	14/4 S to 10/4 S, .560" min to .775" max
indoor/outdoor	Indoor
ip rating	IP67
Material	Rubber
media	Yes
Number of Phases	3.0
Number of Wires	4
Phase	3
Poles	3-way
Voltage	480.0 V
Voltage Rating	480
Wire Size	14-10



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000

Descriptions

Description	TURNLOK PLUG IP67 20A 3PH 480V L1620P ANTI-MIC
extra long description	P&S 26W76AM TLPL IP67 20A 3PH 480V
Features	Antimicrobial Protection
Long Description	SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure
Product Type	TLPL IP67 20A 3PH 480V L1620P Anti-Mic
Special Features	Rated watertight for 1,500 psi high-pressure hosedown, P&S Turnlok® watertight plugs & connectors feature rugged construction, multiple seals to ensure protection against the environment and ease of installation.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007057317
Manufacturers Part Number	26W76AM
UPC	785007057317

Taxonomies, Classifications, and Categories

Category Description	Residential receptacles
Type	PLUG

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	10
Weight Per each	0.58



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

217 Innovation Way
37075-0000, TN Hendersonville
Phone: 615-991-2399
Fax: 000-000-0000

Uses, Certifications, and Standards

Application

High-pressure washdowns. Particle build-up. Condensation. Corrosive substances. Food and beverage processing plants can be harsh, challenging environments. Fortunately, we have a full menu of electrical devices that keep things running smoothly while protecting people and equipment. IEC PIN & SLEEVE DEVICES Watertight Plugs & Connectors | Thermoplastic elastomer body resists water, oils, lubricants and soaps while maintaining NEMA 4, 4X, 6, 6P, and IP65, 66, 67 ratings | Ideal for washdown areas — rated wa

environmental conditions

Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

nema rating

L16-20P

Operating Temperature

-40°-60°C

standard

UL Listed, CSA Listed