



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode
79701-0000, TX Midland
Phone: 432-685-3108
Fax: 432-685-3706



2GTL4LP840 2X4 Lay In Led Fixture

Lithonia Lighting - Acuity

Catalog Number	2GTL4LP840
Manufacturer	Lithonia Lighting - Acuity
Description	The 2 FT. By 4 FT. GTL Led Troffer Provides All The Benefits Of An Led Fixture While Maintaining Familiar Look Of A Traditional Fluorescent Fixture. Provides Energy Savings and Is An Ideal Choice For Schools, Offices, Retail, Hospital and Other Applications
Weight per unit	19.6 (lbs/each)
Product Category	Led Recessed Architectural & S

Features

average life	50,000
dimnable	Yes
Hardware	Yes
Lamp Included	Yes
Lamp Type	LED - Static
Material	Steel
Maximum Operating Temperature	25
Power Source	Hardwired
Shape	Rectangular
Voltage Rating	120-277
Warranty	5
Wattage	39

Material, Color, and Finish

Color	White
color rendering index (cri)	80
color temperature	4000
Finish	Matte
Lens Color	Clear
Lens Material	Acrylic
Style	Traditional

Dimensions and Weight

Height	3.5
Length	49
Width	24.0000



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

1001 South Goode
79701-0000, TX Midland
Phone: 432-685-3108
Fax: 432-685-3706

Descriptions

Description	2X4 LAY IN LED FIXTURE
extra long description	LITH 2GTL4 LP840 2x4 LED Recessed T
Long Description	The 2 ft. by 4 ft. GTL LED troffer provides all the benefits of an LED fixture while maintaining familiar look of a traditional fluorescent fixture. Provides energy savings and is an ideal choice for schools, offices, retail, hospital and other applications
Product Type	Troffer

Manufacturer Information

Brand	Lithonia Lighting
GTIN	00753573916581
Manufacturers Part Number	2GTL4 LP840
UPC	753573916581

Taxonomies, Classifications, and Categories

Category Description	Indoor HID Lighting
----------------------	---------------------

Trade Size

aperture size	2x4
---------------	-----

Packaging

Carton	1
Weight	22.499
Weight Per each	19.58

Uses, Certifications, and Standards

Application	Education,Offices & Banks,Retail
environmental conditions	Indoor
Mounting	Recessed
standard	CSADLC Standard