DESCRIPTION

Adjustable Slot Aperture with Black Baffle designed for use with IC or Non-IC AIR-TITE[™] 3" Halo small aperture line and low voltage housings. Trim ring is available in multiple finishes to match interior decor. Slot trim uses MR16 low voltage or GU10 line voltage lamps ideal for accent and task lighting. Slot Aperture trim offers 35° tilt, and 360° orientation within housing.

Catalog #	Туре
Project	
Comments	Date
Prepared by	


SPECIFICATION FEATURES

Cast aluminum trim ring available in Matte White, Black, Satin Nickel, or Tuscan Bronze finishes. Slot Aperture trim incorporates a matte black baffle to control glare. Three pressure springs ensure positive retention in housing.

Trim includes cover glass lens which may be replaced with a variety of media. (Lamps that have integral glass lens do not require use of the cover glass supplied with this trim).

3006 is designed for use with the following Halo H3 small aperture housings:

• Line Voltage Housing (for H36ICAT H36TAT H36RTAT	120V GU 50W 50W 50W	10 lamps). IC Air-Tite Housing Non-IC Air-Tite Housing Non-IC Air-Tite Remodel Housing		
 Low Voltage Housing (for 12V MR16 lamps). 				
H36LVICAT	50W	IC Air-Tite Housing		
H36LVTAT	50W	Non-IC Air-Tite Housing		
H36LVRTAT	50W	Non-IC Air-Tite Remodel Housing		
H36LVTAT277	50W	Non-IC Air-Tite Housing, 120/277V		
H36LVRTAT277	50W	Non-IC Air-Tite Remodel Housing, 120/277V		
• Line Voltage Housing (for 120V GU10 lamps).				
H38ICAT	50W	IC Air-Tite Housing		
 Low Voltage Housing (for 12V MR16 lamps). 				
H38LVICAT	37W	IC Air-Tite Housing		



 Trim Aperture
 1-1/4" x 2" [32mm x 51mm]

 Ceiling Opening:
 3-3/4" [95mm]

 Outside Diameter:
 4-1/4" [108mm]

ORDERING INFORMATION

SAMPLE NUMBER: 3006WHBB

Order housing and trims separately.

Trim	Finish
3006= 3" Slot Aperture Trim	WHBB=White with Black Baffle BKBB=Black with Black Baffle SNBB=Satin Nickel with Black Baffle TBZBB=Tuscan Bronze with Black Baffle




3006WHBB White with Black Baffle

Halo



3006BKBB Black with Black Baffle



3006SNBB Satin Nickel with Black Baffle



3006TBZBB Tuscan Bronze with Black Baffle

3006

3" Adjustable Slot Aperture Trim

3" TRIMS



Specifications and dimensions subject to change without notice.