

## ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2202 East Rusk Street 75766-0000, TX Jacksonville Phone: 903-586-2904

Fax: 903-586-5271



## 30088J In-Sure Push-In Wire Conn, 88 6-PRT Blue, 100/Jar Ideal

luear		
Catalog Number	30088J	
Manufacturer	Ideal	
Description	Push-In Wire Connector, Blue Insulation Color, +221 °F Operating Temperature, 0.607 In Overall Length, 0.603 In Overall Width, 0.729 In Overall Height, 600 V (Building Wire);1000 V (Maximum Signs/Lighting Fixture), 0.01 LB	
Weight per unit	1.2 (lbs/each)	
Product Category	Electrical Fixture Conn ( Nuts	
Features		
connection	6 Stacked Ports	
Voltage Rating	600 V Maximum Building Wire, 1000 V Maximum Signs And Lighting Fixtures	
Wire Size	#12 AWG - #20 AWG Solid, #14 AWG - #16 AWG (19 Strand Or Less) #18 AWG (7 Strand Or Less) Stranded, #12 AWG - #14 AWG (19 Strand Or Less) #16 AWG (26 Strand Or Less) 318 AWG (16 Strand Or Less) Stranded (Tin Bonded)	
Wire Type	Solid, Stranded, Stranded (Tin Bonded)	
Material, Color, and Finish	X	
Color	Blue	
Dimensions and Weight		
Size	0.607 IN Length X 0.603 IN Width X 0.729 IN Height	
Descriptions		
Description	IN-SURE PUSH-IN WIRE CONN, 88 6-PRT BLUE, 100/JAR	
Features	The In-Sure Push-In Wire Connector is perfect for residential, light commercial, lighting retrofit, and pre-fab wiring systems, or any other branch circuit wiring application where a traditional twist-on wire connector would be used. Simply push the wire in – the low insertion force makes it easy. The color-coded shell allows for quick identification of port configuration while the clear polycarbonate housing allows for visual verification of every connection. The ergonomic design is easier to grip which me	
Manufacturer Information		
Brand	Ideal	
GTIN	00783250460823	
UPC	783250460823	



## ELLIOTT ELECTRIC SUPPLY 2202 East Rusk Street 75766-0000, TX Jacksonville Phone: 903-586-2904 February 202 E86-5271

We Deliver...Lower Cost, Quality Products, & Personal Service

Fax: 903-586-5271

Taxonomies, Classifications, and Categories		
	WIRE NUTS	
Туре	Push-In	
Availability		
Manufacturer Status	Inactive	
minimum qty	100	
Status	Inactive	
Packaging		
Carton	100	
Package	600	

Uses, Certifications, and Standards		
standard	CSA C22.2 #188, 486C/467 UL Listed, RoHS	
Temperature Rating	105 DEG C Shell Rated	

Weight Per each 1.18